

## ● Order No. Example

**TB 77MXL 6.4**  
**TBU**

Belt Nominal Width

Type    Belt Nominal Length

mMaterial	Belt Nominal Width
TB=Rubber	4.8=(4.8mm), 6.4=(6.4mm) 9.5=(9.5mm), 12.7=(12.7mm)
TBU=Polyurethane	6.4=(6.4mm), 9.5=(9.5mm)

**J** Decimal points (mm) are used to display the belt nominal width of MXL.

Type		Belt Nominal Length	No. of Teeth	Belt Pitch Circumference (mm)	¥				¥	
TB	TBU				Rubber				Polyurethane	
					4.8	6.4	9.5	12.7	6.4	9.5
○		45MXL	45	91.44						
○		48MXL	48	97.54						
○		50MXL	50	101.60						
○		52MXL	52	105.66						
○		53MXL	53	107.70						
○		54MXL	54	109.73						
○		55MXL	55	111.76						
○		56MXL	56	113.79						
○		57MXL	57	115.82						
○		59MXL	59	119.89						
○		60MXL	60	121.92						
○		61MXL	61	123.95						
○		63MXL	63	128.02						
○		65MXL	65	132.08						
○		67MXL	67	136.14						
○		68MXL	68	138.18						
○		70MXL	70	142.24						
○		71MXL	71	144.27						
○		72MXL	72	146.30						
○		73MXL	73	148.34						
○		75MXL	75	152.40						
○		76MXL	76	154.43						
○	○	77MXL	77	156.46						
○	○	78MXL	78	158.50						
○		79MXL	79	160.53						
○	○	80MXL	80	162.56						
○	○	82MXL	82	166.62						
○	○	83MXL	83	168.66						
○	○	85MXL	85	172.72						
○	○	87MXL	87	176.78						
○	○	88MXL	88	178.82						
	○	89MXL	89	180.85						
○	○	90MXL	90	182.88						
○	○	91MXL	91	184.91						
○		92MXL	92	186.94						
○		93MXL	93	188.98						
○	○	94MXL	94	191.01						
○	○	95MXL	95	193.04						
○		96MXL	96	195.07						
○		97MXL	97	197.10						