




# 50A

## ● Order No. Example



- Chain .....No.50
- Chain Pitch .....(P)15.875mm
- Roller Link Inner Width .....(W) 9.53 mm
- Roller Outside Diameter .....(Dr)10.16 mm
- Tooth Width .....(T) 8.7 mm

 Common Steel

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum			
50A	10	58	51.37	10	11	0.14		
	11	64	56.35	12	13	0.17		
	12	69	61.34	12	13	0.20		
	13	74	66.34	12	13	0.23		
	14	79	71.34	12	13	0.27		
	15	84	76.35	12	13	0.30		
	16	89	81.37	14	15	0.35		
	17	94	86.39	14	15	0.40		
	18	100	91.42	14	15	0.45		
	19	105	96.45	14	15	0.48		
	20	110	101.48	14	15	0.50		
	21	115	106.51	14	15	0.60		
	22	120	111.55	16	17	0.66		
	23	125	116.58	16	17	0.72		
	24	130	121.62	16	17	0.78		
	25	135	126.66	16	17	0.85		
	26	140	131.70	16	17	0.90		
	27	145	136.74	16	17	1.00		
	28	150	141.79	16	17	1.05		
	29	155	146.83	16	17	1.12		
	30	161	151.87	16	17	1.20		
	31	166	156.92	16	17	1.30		
	32	171	161.96	16	17	1.35		
	33	176	167.01	16	17	1.45		
	34	181	172.05	16	17	1.55		
	35	186	177.10	16	17	1.65		
	36	191	182.14	19	20	1.75		
	37	196	187.19	19	20	1.85		
	38	201	192.24	19	20	1.95		
	39	206	197.29	19	20	2.05		