

# B-BOX® ビーボックス

B-BOXES (BS)



**ボディ (A5056、A6061、A6063) アルミニウム 黒色アルマイト処理 シャフト (SUS303)**  
**Material : Body-Aluminium (ISO AlMg5, AlMg1SiCu, AlMg0.7Si) with Anodize treated Shaft-Stainless steel**

単位 : mm  
 Dimensions : mm

商品記号 Catalogue Number	形 Type	レシオ Gear Ratio	Z	Y	□ C	A	B	軸径 Shaft φD(h7)	E
BS 35 L - 001	L	1	-	-	14	35	27	φ 3	8
BS 45 L - 001	L	1	-	-	18	45	33	φ 4	12
BS 65 L - 001	L	1	-	-	25	65	50	φ 6	15
BS 80 L - 001	L	1	-	-	30	80	60	φ 8	20
BS 90 L - 001	L	1	-	-	35	90	70	φ10	20
BS 105 L - 001	L	1	-	-	40	105	80	φ12	25
BS 65 L - 002	L	2	-	-	25	65	50	φ 6	15
BS 80 L - 002	L	2	-	-	30	80	60	φ 8	20
BS 90 L - 002	L	2	-	-	35	90	70	φ10	20
BS 105 L - 002	L	2	-	-	40	105	80	φ12	25
BS 45 T - 001	T	1	72	48	18	45	33	φ 4	12
BS 65 T - 001	T	1	105	75	25	65	50	φ 6	15
BS 80 T - 001	T	1	130	90	30	80	60	φ 8	20
BS 90 T - 001	T	1	145	105	35	90	70	φ10	20
BS 105 T - 001	T	1	170	120	40	105	80	φ12	25
BS 65 T - 002	T	2	105	75	25	65	50	φ 6	15
BS 80 T - 002	T	2	130	90	30	80	60	φ 8	20
BS 90 T - 002	T	2	145	105	35	90	70	φ10	20
BS 105 T - 002	T	2	170	120	40	105	80	φ12	25

D 軸の位相は一致しておりません。  
 Directions of the D-cut shaft face are not fixed.

特殊仕様および追加工（使用環境、オイルリーク対策、軸径追加工等取付方法）についてはご相談下さい。  
 Please do not hesitate to contact us for special method of installation, checking on the usage environment and work out of oil leaks.



GOOD DESIGN AWARD 2010  
**LONG LIFE  
 DESIGN AWARD**