



SUSFBN80B

SUS FBN Stainless Steel Finished Bore Sprocket New JIS Keyway Specification

● Order No. Example

SUS FBN 80B 15 D30




- Chain No.80
- Chain Pitch (P)25.4 mm
- Roller Link Inner Width (W)15.88mm
- Roller Outside Diameter (Dr)15.88mm
- Tooth Width (T)14.6 mm

 Stainless Steel  S304

Type	No. of Teeth	φDH7	Outer Diameter Do	Pitch Diameter Dp	Boss Diameter BD	Boss Length BL	a	Weight kg	No. of Teeth	¥
SUS FBN 80B	10	25 30	93	82.19	52	40	12	1.02	10	
	12	25 30	110	98.14	67	40	12	1.60	12	
	13	25 30	118	106.14	77	40	12	1.90	13	
	14	25 30	127	114.15	77	40	12	2.15	14	
	15	25 30	135	122.17	93	40	12	2.30	15	
	16	30 35	143	130.20	93	40	12	2.50	16	
	20	35 40	176	162.37	93	40	12	3.60	20	


Shaft Hole Machined Specification

φDH7	Keyway bxt ²	Set Screw M
25 - 30	8 x 3.3	8
32 - 38	10 x 3.3	8
40	12 x 3.3	8




and Quantity

Order Method



Same-day shipping

Postage



Guide

* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.