


両ニップル〈N〉  
片ニップル〈NS〉

材質：SUS304




単位：mm

呼び径		長さ L
(A)	(B)	
6	1/8	24
8	1/4	26
10	3/8	28
15	1/2	34
20	3/4	38
25	1	42
32	1 1/4	50
40	1 1/2	50
50	2	58
65	2 1/2	70
80	3	78
100	4	90

両長ニップル〈NL〉  
片長ニップル〈NSL〉

材質：SUS304




単位：mm

呼び径		長さ					
(A)	(B)	L					
6	1/8	50	75	100	125	150	200
8	1/4	50	75	100	125	150	200
10	3/8	50	75	100	125	150	200
15	1/2	50	75	100	125	150	200
20	3/4	50	75	100	125	150	200
25	1	50	75	100	125	150	200
32	1 1/4	75	100	125	150	200	
40	1 1/2	75	100	125	150	200	
50	2	75	100	125	150	200	
65	2 1/2			100	125	150	200
80	3			100	125	150	200
100	4			100	125	150	200

ホースニップル〈HN〉

材質：SUS304



単位：mm

呼び径		長さ L	E×数
(A)	(B)		
6	1/8	41	4.3×4
8	1/4	41	4.3×4
10	3/8	42	4.3×4
15	1/2	52	6×4
20	3/4	55	6×4
25	1	60	6×4
32	1 1/4	66	8×4
40	1 1/2	70	8×4
50	2	80	8×4
65	2 1/2	150	11×4
80	3	150	11×4
100	4	150	11×4