



Order No. Example

80SD 15



- ChainNo.80
- Chain Pitch(P)25.4 mm
- Roller Link Inner Width(W)15.88mm
- Roller Outside Diameter(Dr)15.88mm
- Tooth Width(T)14.6 mm (C)45.4mm

m Carbon Structural Steel

h High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum	Maximum					
80SD	10	93	82.19	20	21	32	52	60	1.60		
	11	102	90.16	20	21	40	60	60	2.04		
	12	110	98.14	20	21	46	67	60	2.52		
	13	118	106.14	20	21	51	77	60	3.04		
	14	127	114.15	20	21	57	85	60	3.60		
	15	135	122.17	20	21	63	93	60	4.16		
	16	143	130.20	20	21	70	102	60	4.89		
	17	151	138.23	20	21	75	110	60	5.61		
	18	159	146.27	23	24	80	118	60	6.36		
	19	167	154.32	23	24	80	126	60	7.13		
	20	176	162.37	23	24	95	134	60	8.03		
	21	184	170.42	23	24	95	142	60	8.88		
	22	192	178.48	23	24	106	151	60	9.93		
	23	200	186.54	23	24	110	159	60	10.94		
	24	208	194.60	23	24	115	167	60	11.98		
	25	216	202.66	23	24	124	175	60	13.08		
	26	224	210.72	23	24	130	183	60	14.24		
	27	233	218.79	23	24	135	191	60	15.50		
	28	241	226.86	23	24	140	199	60	16.75		
	29	249	234.93	23	24	148	207	60	18.04		
	30	257	243.00	23	24	155	216	60	19.38		

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.



Order Method

Sprocket No. and Quantity



Postage

Same-day shipping



Guide

* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.