



MRC コレットチャックホルダ

COLLET CHUCK HOLDER



BT50

CODE	FIG	ϕd	L	D	G	C	θ	H
BT50-MRC10	1	0.5 ~ 10.0	150	28	M11 × P1.0	-	-	-
			200			-	-	
			250			50	12°	
	2		300			71	12°	
			350			70	8°	
BT50-MRC13	1	1.0 ~ 13.0	150	35	M15 × P1.5	-	-	-
			200			-	-	
			250			55.5	12°	
	2		300			62	8°	
			350			-	-	
BT50-MRC16	1	1.0 ~ 16.0	150	42	M18 × P1.5	-	-	-
			200			-	-	
			250			-	-	
	2		300			61	12°	
			350			-	-	
BT50-MRC20	1	2.0 ~ 20.0	100	50	M22 × P1.5	-	-	-
			150			-	-	
			200			-	-	
			250			-	-	
			300			-	-	
350	-	-						

■ナットは付属していますが、コレット、レンチは別途ご注文ください。 Comes with collet nut, purchase collet & wrench separately.
 普通コレットMRC10~MRC20 P33 タップコレット P36

レンチ

WRENCH

CODE	L	適用するナット Nut Size
MRS-10	E16P 145	MRC10 - Hi-Q - ERB16
MRS-13	E20P 172	MRC13 - Hi-Q - ERB20
MRS-16	E25 210	MRC16 - Hi-Q - ERB25
MRS-20	E32 250	MRC20 - Hi-Q - ERB32



ナット締付推奨トルク


CODE	NUT	Nm
MRC10	HiQ-ERB16	39
MRC13	HiQ-ERB20	46
MRC16	HiQ-ERB25	78
MRC20	HiQ-ERB32	115

クーラントシール付き調整ネジ

BACK-UP SCREW W/COOLANT SEAL

適合するホルダ

CODE	d	D	L	H	h	Holder Size
MRMC11	M11 P=1.0	9	15	10	2.5	MRC10
MRMC15	M15 P=1.5	12	18	13	3	MRC13
MRMC18	M18 P=1.5	15	19			MRC16
MRMC22	M22 P=1.5	19	19	4	MRC20	



高圧用バックアップスクリュー

BACK-UP SCREW FOR HIGH PRESSURE

CODE	d	D	L	H	h	O-ring
HRMS11	M11P=1.0	8	25	10	2.5	N 4
HRMS15	M15P=1.5	12			3	P 6
HRMS18	M18P=1.5	15	30	10	4	P 9
HRMS22	M22P=1.5	19			5	P12

