




L050 Type

K-Timing Pulley <Prepared Hole Product>


● Order No. Example

K 20 L050 BF (Type)
 STYLE No. of Teeth Type Shape
 Timing Pulley No. L050
 W: 14
 H: 2.5



AF

BF



AF Type

BF Type

The KANA Timing Pulley achieves clean transmission thanks to its low noise that comes by way of its excellent timing transmission performance.

Type	No. of Teeth	Shape	Dp	Do	LA	LB	K	D	d		F	M	Compatible Flanges	Pulley Approx. Weight kg	
									min	max				AF	BF
L 050	10	AF, BF	30.32	29.56	19	31	12	20	6	14	35	22	KTF-103522	0.08	0.14
	12	AF, BF	36.38	35.62	19	31	12	25	8	18	43	28	KTF-104328	0.12	0.21
	14	AF, BF	42.45	41.68	19	31	12	30	10	20	47	34	KTF-104734	0.17	0.29
	15	AF, BF	45.48	44.72	19	31	12	32	10	20	51	36	KTF-165136	0.20	0.34
	16	AF, BF	48.51	47.75	19	31	12	34	12	22	55	39	KTF-165539	0.23	0.38
	17	AF, BF	51.54	50.78	19	31	12	35	12	22	57	41	KTF-165741	0.26	0.43
	18	AF, BF	54.57	53.81	19	31	12	36	12	24	61	41	KTF-166141	0.30	0.47
	19	AF, BF	57.61	56.84	19	31	12	38	12	24	65	50	KTF-166550	0.33	0.53
	20	AF, BF	60.64	59.88	19	31	12	40	12	26	65	50	KTF-166550	0.37	0.59
	21	AF, BF	63.67	62.91	19	31	12	42	12	26	69	50	KTF-166950	0.42	0.66
	22	AF, BF	66.70	65.94	19	31	12	44	12	28	74	53	KTF-167453	0.46	0.72
	24	AF, BF	72.77	72.00	19	31	12	44	12	28	78	58	KTF-167858	0.55	0.82
	25	AF, BF	75.80	75.04	19	31	12	44	12	28	83	63	KTF-168363	0.60	0.87
	26	AF, BF	78.83	78.07	19	31	12	44	12	28	86	66	KTF-168666	0.66	0.92
	28	AF, BF	84.89	84.13	19	31	12	50	12	30	93	75	KTF-169375	0.77	1.11
	30	AF, BF	90.96	90.20	19	31	12	50	12	30	99	78	KTF-169978	0.89	1.23
	32	AF, BF	97.02	96.26	19	34	15	50	16	30	105	84	KTF-1610584	1.01	1.38
	34	AF, BF	103.08	102.32	19	34	15	56	16	32	112	90	KTF-1611290	1.14	1.62
	36	AF, BF	109.15	108.39	19	34	15	56	16	32	115	90	KTF-1611590	1.29	1.77
	38	AF, BF	115.21	114.45	19	34	15	60	16	34	126	100	KTF-16126100	1.42	1.97
40	AF, BF	121.28	120.51	19	34	15	60	16	34	126	100	KTF-16126100	1.61	2.16	
42	AF, BF	127.34	126.58	19	34	15	60	16	34	131	101	KTF-16131101	1.78	2.33	
44	AF, BF	133.40	132.64	19	39	20	65	16	38	138	125	KTF-16138125	1.96	2.73	



Timing Pulley No. and Quantity

Order Method



Guide

* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.



Postage

Same-day shipping



Precautions

* The prepared hole diameter is finished at the minimum diameter H7. Comes with a flange.