

**PS254**  
Horizontal two-shaft hole for shaft or PS204 attachment

φ13×25

**PS255**  
Decorating ball for attachment on the shaft edge

sphere φ13

**PS263,PS264**  
Screw holes dowel It can be used for a setting up from the flat surface or inserting it into a hole of φ6 or fixing a screw.

PS263

1 bag for 2 parts

φ6×14  
(stainless steel)

Part No.	M
PS263	3
PS264	4

**PS270**  
For hinge one-side free with the other side fixed

φ15×31

**PS271**  
Parts attachment for sensor or parts attachment

1 bag for 2 parts

6×6×44

**PS272**  
Parts attachment for sensor or parts attachment

1 bag for 2 parts

φ6×60  
(stainless steel)

Examples of fixing switch

**PS300**  
Corner for external tightening to set the corner of frame assembly

23×23×18

**PS305**  
Low-profile corner for External tightening to be nearly flat for pipe and clamp top

23×23×13

**PS400**  
Split T to tuck without disassembling frame (capable of later attachment)

22×18×11

**PS401**  
Split T to tuck without disassembling frame (capable of later attachment)

15×18×11

**PS403**  
Split T to tuck without disassembling frame (capable of later attachment)

20×20×11

**PS523**  
Two screw tapped for parts or board attachment

20×15×8

**PS600**  
Horizontal hole to raise horizontal and vertical shaft

18×26×8

**PS601,PS602**  
Vertical hole to fix vertical shaft

Screw cap to be on the opposite side against PS601

PS601

PS602

15×26×14

**PS603**  
Flange for lateral side or vertical shaft attachment

8×26×17

●For 300, 400 type, please match the mark on both edge phase on assembly.