




SRBS Hexalobular Button Head Cap Screws with Pin

WEB Selection Tool
 WEB CAD Download
 Tamper Resistance
 SUS Stainless steel



● Part number specification

SRBS-M5 - 16



Order in number of packs.
The minimum order quantity is 1 piece. → P.794

- Button head cap screws with pin at the center of their hexalobular* socket.
- Screws cannot be installed or removed by using standard tools.
- Install and remove by using **SRX** Specialty Hexalobular Key.

*The hexalobular shape is prescribed by JIS B 1015 : 2008 (ISO 10664 : 2005) "Hexalobular internal driving feature for bolts and screws".

● Application

Machinery, tools, equipment, and devices disassembly prevention · tampering prevention, theft prevention for outdoor facilities, security measures, and safety measures

● Material/Finish

RoHS Compliant

	SRBS
Main Body	SUS304
Strength Class	Equivalent to A2-50

Unit : mm

Part Number	M	L										D1	L1	Applicable wrench	Hexalobular Socket No.	Mass (g)
SRBS-M3	M3	6	8	10	12	16	20	25				5.7	1.65	SRX-10	10	0.48 - 1.4
SRBS-M4	M4		8	10	12	16	20	25	30			7.6	2.2	SRX-20	20	1.2 - 3.2
SRBS-M5	M5			10	12	16	20	25	30	40		9.5	2.75	SRX-25	25	2 - 6.4
SRBS-M6	M6			10	12	16	20	25	30	40	50	10.5	3.3	SRX-30	30	3.3 - 12
SRBS-M8	M8			10	12	16	20	25	30	40	50	14	4.4	SRX-40	40	7.3 - 22


Part Number	Qty*1 per pack
SRBS-M3	20
SRBS-M4	20
SRBS-M5	20
SRBS-M6	10
SRBS-M8	10

*1 The minimum order quantity is 1 piece. → P.794

● Dedicated wrench

Unit : mm

Part Number	L1	L2	Mass (g)	Qty per pack
SRX-10	60	20	3.7	1
SRX-20	67	23	8.2	1
SRX-25	70	25	11	1
SRX-30	81	28	20	1
SRX-40	88	31	32	1



Individual Sales → P.794
 Cleanroom Wash & Packaging → P.792
 Screw Length Adjustment → P.796
 Vibration Resistant → P.795
 Modification process for captive use → P.791