



KYTS 三角ノブ

GN5339.5

CAD DATA [2D](#) [3D](#)
 download




KYTS-M




KYTS-K




KYTS-R



KYTS-K



KYTS-M



KYTS-R

- 耐蝕性にすぐれたステンレス製。
- にぎりやすい形状です。
- **KYTS-K** ————— めねじ・貫通穴
- **KYTS-M** ————— めねじ
- **KYTS-R** ————— リーマ穴
- 材質・仕上げ
 SCS13(SUS304相当)、ショットブラスト

ご注文にあたって

14:00当日出荷

直送可能

品番

KYTS-50×M8

三角ノブ

D

M (めねじ)

KYTS-K (めねじ・貫通穴)

unit:mm

Catalog Number 品番	Price (Yen) 価格 (円)	D	M	Lf	H	s	d	Mass 質量 (g)
KYTS-32×K 6	2,830	32	M 6	10	21	12	12	42
KYTS-40×K 8	3,500	40	M 8	13	26	14	14	82
KYTS-50×K10	4,480	50	M10	16	33	19	18	146
KYTS-60×K12	6,100	60	M12	20	41	23	20	270

KYTS-M (めねじ)

unit:mm

Catalog Number 品番	Price (Yen) 価格 (円)	D	M	Lf	H	s	d	Mass 質量 (g)
KYTS-32×M 5	2,830	32	M 5	10	21	12	12	45
KYTS-32×M 6	2,830	32	M 6	12	21	12	12	44
KYTS-40×M 6	3,500	40	M 6	12	26	14	14	87
KYTS-40×M 8	3,500	40	M 8	15	26	14	14	85
KYTS-50×M 8	4,480	50	M 8	15	33	19	18	155
KYTS-50×M10	4,480	50	M10	18	33	19	18	152
KYTS-60×M10	6,100	60	M10	18	41	23	20	287
KYTS-60×M12	6,100	60	M12	22	41	23	20	278

KYTS-R (リーマ穴)

unit:mm

Catalog Number 品番	Price (Yen) 価格 (円)	D	RH ⁷	Lr	H	s	d	Mass 質量 (g)
KYTS-32×R 6	2,830	32	6	10	21	12	12	44
KYTS-40×R 8	3,500	40	8	12	26	14	14	85
KYTS-50×R10	4,480	50	10	15	33	19	18	152
KYTS-60×R12	6,100	60	12	18	41	23	20	278