


SPS-C Plastic Screw - Socket Head Cap Screws - PPS



Selection Tool
 CAD Download
 Heat-resistance
 Chemical-proof



● Material/Finish

RoHS Compliant

SPS-C	
Main body	PPS (Polyphenylene Sulfide) /Bright Light Brown Glass Fiber 40%
Heat Resistance Temperature*	200°C

*This is the value for the plastic material. The maximum operating temperature of the product changes with performance conditions such as tightening torque.

- PPS has excellent heat resistance and chemical resistance and continuous duty temperature of 200 deg C. Under 200 deg C, no oils, fats, or organic solvents dissolve PPS.
- It has high strength, high rigidity, and high heat resistance strength.
- It has high incombustibility that meets V-0 of UL 94.
- The properties and precautions of plastic screws
➔ P.724

● Application

FPD production equipment, semiconductor devices, printed circuit board etching devices, metallic surface treatment equipment and facilities, chemical plants, transformers, electrical and electronic equipment, hot water pumps, and chemical pumps

Unit : mm

Part Number	M	L								D1	L1	B	Tension*1 Rupture Load (N)	Torsional*1 Torque (N·m)	Mass (g)	
		6	8	10	12	15	20	25	30							40
SPS-M3-C	M3	6	8	10	12	15	20			5.5	3	2.5	570	0.36	0.15 - 0.29	
SPS-M4-C	M4	6	8	10	12	15	20			7	4	3	980	0.71	0.32 - 0.56	
SPS-M5-C	M5		8	10	12	15	20	25	30	8.5	5	4	1570	1.42	0.52 - 1.2	
SPS-M6-C	M6			10	12	15	20	25	30	40	10	6	5	2250	2.11	1 - 2.3
SPS-M8-C	M8			10	12	15	20	25	30	40	13	8	6	3720	5.29	2.2 - 4.4

*1 Values in chart are for reference only. They are not guaranteed values. The recommendation torque is 50% of the torsional torque.

Part Number	Qty per pack*1
SPS-M3-C	20
SPS-M4-C	20
SPS-M5-C	10
SPS-M6-C	10
SPS-M8-C	5

*1 The minimum order quantity is 1 piece. ➔ P.794

● Part number specification

SPS - M5 - 20 - C

Product Code **1** **2** Product Code

Order in number of packs.
The minimum order quantity is 1 piece. ➔ P.794

Individual Sales ➔ P.794
 Cleanroom Wash & Packaging ➔ P.792
 Screw Length Adjustment ➔ P.796
 Vibration Resistant ➔ P.795
 Modification process for captive use ➔ P.791
 Available / Add'l charge Available / Add'l charge Available / Add'l charge Not Available Please feel free to contact us