



- With / without grip mounting hole can be selected by the end symbol of the part number.
 - AH** ——— With grip mounting hole
 - AH-N** ——— Without grip mounting hole
- No grip is supplied with this product. Please separately order a grip. → P.395 List of grips
- Material/Finish RoHS Compliant

	AH
Main body	AC8A Buffing (Rim Part Only)

Part Number With grip mounting holes	M	P	Part Number Without grip mounting holes	Unit : mm									Number of spokes	Mass (g)
				D	H	A	E	s	d	L				
AH-80	M5	33	AH-80-N	80	26	10	15	16	28	25		95		
AH-100	M5	42	AH-100-N	100	26	11	15	15	33	25		215		
AH-125	M6	53.5	AH-125-N	125	32	14	15	18	33	30	2	225		
AH-140	M6	62	AH-140-N	140	32	14	15	18	38	30	2	335		
AH-160	M8	68	AH-160-N	160	36	15	16	21	40	35	2	415		
AH-200	M10	87.5	AH-200-N	200	41	16	17	25	48	40	3	720		
AH-250	M10	112	AH-250-N	250	42	19	20	23	52	40	3	1070		
AH-300	M10	137	AH-300-N	300	47	19	22	28	57	45	3	1360		

• Recommended applicable grip

Part Number	Recommended applicable grip			
	GNTR → P.410	GTR → P.411	GTM → P.415	HS → P.417
AH-80	GNTR-18 - M5	GTR-18 - M5	GTM-18 - M5	HS-5
AH-100	GNTR-18 - M5	GTR-18 - M5	GTM-18 - M5	HS-5
AH-125	GNTR-19 - M6	GTR-19 - M6	GTM-19 - M6	HS-6
AH-140	GNTR-19 - M6	GTR-19 - M6	GTM-19 - M6	HS-6
AH-160	GNTR-24 - M8	GTR-24 - M8	GTM-24 - M8	HS-8
AH-200	GNTR-28 - M10	GTR-28 - M10	GTM-28 - M10	HS-10
AH-250	GNTR-28 - M10	GTR-28 - M10	GTM-28 - M10	HS-10
AH-300	GNTR-28 - M10	GTR-28 - M10	GTM-28 - M10	HS-10

• Part number specification

AH - 80 - N

Product Code ◀ 1 ▶ 2

Cleanroom Wash & Packaging → P.792	Vibration Resistant → P.795	Laser Marking → P.806	Modification of Shaft Hole Diameter → P.800
Available / Add'l charge	Not Available	Available / Add'l charge	Available / Add'l charge