




RoHS Compliant

ERON®

No.E-400

Stud Bolts

Material S45C **Heat Treatment** HRC30 ± 5 heat treatment
Surface Treatment Blackened



Specifications

Order No.	No.	Screw Diameter (Coarse Thread)	A	B	Weight (g)		
01117	BM00850	M8×1.25	50	22	20		
02711	BM00875	M8×1.25	75	30	30		
02712	BM08100	M8×1.25	100	40	40		
00036	BM08125	M8×1.25	125	40	50		
02713	BM08150	M8×1.25	150	40	60		
02714	BM08175	M8×1.25	175	40	70		
02715	BM08200	M8×1.25	200	40	80		
02716	BM01050	M10×1.5	50	22	31		
02717	BM01075	M10×1.5	75	30	47		
02718	BM10100	M10×1.5	100	40	63		
02719	BM10125	M10×1.5	125	40	78		
02720	BM10150	M10×1.5	150	40	94		
02721	BM10175	M10×1.5	175	40	109		
02722	BM10200	M10×1.5	200	40	125		
02723	BM01250	M12×1.75	50	22	35		
02724	BM01275	M12×1.75	75	30	55		
02725	BM12100	M12×1.75	100	40	70		
02726	BM12125	M12×1.75	125	40	95		
02727	BM12150	M12×1.75	150	40	115		
02728	BM12175	M12×1.75	175	40	140		
02729	BM12200	M12×1.75	200	40	160		
16420	BM12225	M12×1.75	225	60	180		
16421	BM12250	M12×1.75	250	60	200		
16422	BM12300	M12×1.75	300	60	240		
16423	BM12350	M12×1.75	350	60	285		
16424	BM12400	M12×1.75	400	60	330		
16425	BM12450	M12×1.75	450	60	375		
16426	BM12500	M12×1.75	500	60	420		
02730	BM01450	M14×2	50	22	61		
02731	BM01475	M14×2	75	30	92		
02732	BM14100	M14×2	100	40	123		
02733	BM14125	M14×2	125	40	153		
00120	BM14150	M14×2	150	40	184		
02734	BM14175	M14×2	175	40	215		
02735	BM14200	M14×2	200	40	246		
02736	BM14225	M14×2	225	60	276		
02737	BM14250	M14×2	250	60	367		
02738	BM14300	M14×2	300	60	369		
02739	BM14350	M14×2	350	60	430		
02740	BM14400	M14×2	400	60	492		
02741	BM01675	M16×2	75	30	120		
02742	BM16100	M16×2	100	40	160		
02743	BM16125	M16×2	125	40	200		
02744	BM16150	M16×2	150	40	241		
02745	BM16175	M16×2	175	40	281		
02746	BM16200	M16×2	200	40	321		
02747	BM16225	M16×2	225	60	361		
02748	BM16250	M16×2	250	60	401		