

RoHS対応

ERON®

BOX PARALLELS

No.E-126M

ボックスパラレル


材質 FC250

熱処理 焼鈍

表面処理 塗装(黒皮部)

●並列精度は0.04以内です。


使用例



1BOX

機械仕上:▽▽(~)研削・摺合4面仕上:▽▽▽(~▽▽)

研削・摺合6面仕上:▽▽▽▽(~▽▽▽)



ベースエレメント

クランプユニット

ローケーティング
エレメント

クランピング
パーツ

補助ベース

マシンバイス

ボール盤バイス

技術資料

索引

仕様・価格表

タイプ	A	B	C	D	E	質量 kg	機械仕上						研削仕上							
							F	G	6面仕上			F	G	4面仕上			6面仕上			
									オーダーNo.	No.	価格			オーダーNo.	No.	価格	オーダーNo.	No.	価格	
1	100	100	100	(18)	-	5.2	0.020	0.030	37743	BP111M	26,800	0.010	0.015	37715	BP111P	38,800	37769	(BP111PP)	44,300	
	100	100	150	(18)	-	7.8	0.020	0.030	37744	BP112M	31,800	0.010	0.015	37716	BP112P	46,300	37770	(BP112PP)	51,500	
	100	100	300	(18)	-	15.5	0.020	0.030	37745	(BP113M)	63,500	0.010	0.015	37717	(BP113P)	78,500	37771	(BP113PP)	89,500	
	100	100	610	(18)	-	31.5	0.030	0.040	37746	BP114M	108,000	0.015	0.020	37718	(BP114P)	167,000	37772	(BP114PP)	177,000	
	100	150	150	(19.5)	-	8.2	0.020	0.030	37747	BP121M	41,700	0.010	0.015	37719	BP121P	58,500	37773	(BP121PP)	69,000	
	100	150	300	(19.5)	-	16.4	0.020	0.030	37748	(BP122M)	100,000	0.010	0.015	37720	(BP122P)	101,000	37774	(BP122PP)	111,000	
	B	100	150	610	(19.5)	-	33.3	0.030	0.040	37749	BP123M	200,000	0.015	0.020	37721	(BP123P)	224,000	37775	(BP123PP)	257,000
	O	125	125	125	(19.5)	-	7.5	0.020	0.030	37750	BP131M	40,600	0.010	0.015	37722	BP131P	54,500	37776	(BP131PP)	60,500
	X	125	125	300	(19.5)	-	18.0	0.020	0.030	37751	(BP132M)	97,000	0.010	0.015	37723	(BP132P)	111,000	37777	(BP132PP)	121,000
		125	125	610	(19.5)	-	36.6	0.030	0.040	37752	BP133M	233,000	0.015	0.020	37724	(BP133P)	243,000	37778	(BP133PP)	253,000
2	150	150	150	(19.5)	-	10.0	0.020	0.030	37753	BP141M	43,500	0.012	0.018	37725	BP141P	60,000	37779	(BP141PP)	65,500	
	150	150	200	(19.5)	-	13.4	0.020	0.030	37754	BP142M	53,000	0.012	0.018	37726	BP142P	69,500	37780	(BP142PP)	73,500	
	150	150	300	(19.5)	-	20.0	0.020	0.030	37755	(BP143M)	79,000	0.012	0.018	37727	(BP143P)	97,000	37781	(BP143PP)	107,000	
	150	150	610	(19.5)	-	40.7	0.030	0.040	37756	BP144M	191,000	0.018	0.024	37728	(BP144P)	205,000	37782	(BP144PP)	217,000	
	BOX	125	250	250	(22)	22	30.5	0.025	0.040	37757	BP251M	93,000	0.013	0.020	37729	BP251P	110,000	37783	(BP251PP)	120,000
		125	250	300	(22)	22	36.6	0.025	0.040	37758	(BP252M)	110,000	0.013	0.020	37730	(BP252P)	130,000	37784	(BP252PP)	141,000
		125	250	610	(22)	22	74.4	0.040	0.050	37759	BP253M	268,000	0.020	0.026	37731	(BP253P)	282,000	37785	(BP253PP)	292,000
		150	300	300	(22)	26	46.4	0.030	0.050	37760	BP261M	124,000	0.015	0.025	37732	BP261P	141,000	37786	(BP261PP)	152,000
		150	300	610	(22)	26	94.4	0.050	0.060	37761	BP262M	296,000	0.025	0.030	37733	(BP262P)	309,000	37787	(BP262PP)	319,000
		200	200	200	(25)	21	30.1	0.030	0.050	37762	BP271M	86,500	0.015	0.025	37734	BP271P	101,000	37788	(BP271PP)	107,000
200		200	300	(25)	21	45.2	0.030	0.050	37763	(BP272M)	129,000	0.015	0.025	37735	(BP272P)	145,000	37789	(BP272PP)	150,000	
200		200	610	(25)	21	92.0	0.050	0.060	37764	BP273M	312,000	0.025	0.030	37736	BP273P	321,000	37790	(BP273PP)	331,000	
250		250	250	(25)	26	50.6	0.030	0.050	37765	BP281M	143,000	0.015	0.025	37737	BP281P	158,000	37791	(BP281PP)	168,000	
250		250	300	(25)	26	60.7	0.030	0.050	37766	(BP282M)	173,000	0.015	0.025	37738	(BP282P)	189,000	37792	(BP282PP)	198,000	
250	250	610	(25)	26	123.3	0.050	0.060	37767	BP283M	415,000	0.025	0.030	37739	(BP283P)	422,000	37793	(BP283PP)	435,000		