


■ 複列アンギュラ玉軸受

内径：10～45mm



1N=0.102kgf

主要寸法 (mm)				呼び番号								基本動定格荷重 Cr (N)		基本静定格荷重 Cor (N)	
d	D	B	r _(最小)	開放形	シールド形			シールド形		輪溝付	止め輪付				
10	30	14.3	0.6	5200	5200Z	5200ZZ	5200NS	5200-2NS	5200N	5200NR	7300	4000			
	30	14.3	0.6	5200A	5200AZ	5200AZZ	5200ANS	5200A-2NS	5200AN	5200ANR	6950	3800			
12	32	15.9	0.6	5201	5201Z	5201ZZ	5201NS	5201-2NS	5201N	5201NR	10700	5950			
	32	15.9	0.6	5201A	5201AZ	5201AZZ	5201ANS	5201A-2NS	5201AN	5201ANR	10300	5650			
15	35	15.9	0.6	5202	5202Z	5202ZZ	5202NS	5202-2NS	5202N	5202NR	11900	7200			
	35	15.9	0.6	5202A	5202AZ	5202AZZ	5202ANS	5202A-2NS	5202AN	5202ANR	11400	6850			
17	40	17.5	0.6	5203	5203Z	5203ZZ	5203NS	5203-2NS	5203N	5203NR	15000	9250			
	40	17.5	0.6	5203A	5203AZ	5203AZZ	5203ANS	5203A-2NS	5203AN	5203ANR	14200	8800			
	47	22.2	1	5303	—	—	—	—	5303N	5303NR	21300	12700			
20	47	20.6	1	5204	5204Z	5204ZZ	5204NS	5204-2NS	5204N	5204NR	20000	12700			
	47	20.6	1	5204A	5204AZ	5204AZZ	5204ANS	5204A-2NS	5204AN	5204ANR	19000	12100			
	52	22.2	1.1	5304	—	—	—	—	5304N	5304NR	21700	13300			
25	52	20.6	1	5205	5205Z	5205ZZ	5205NS	5205-2NS	5205N	5205NR	21800	15100			
	52	20.6	1	5205A	5205AZ	5205AZZ	5205ANS	5205A-2NS	5205AN	5205ANR	20600	14300			
	62	25.4	1.1	5305	—	—	—	—	5305N	5305NR	32000	21600			
30	62	23.8	1	5206	—	—	—	—	5206N	5206NR	30500	21700			
	62	23.8	1	—	5206Z	5206ZZ	5206NS	5206-2NS	—	—	25900	18700			
	62	23.8	1	5206A	—	—	—	—	5206AN	5206ANR	28600	20500			
	62	23.8	1	—	5206AZ	5206AZZ	5206ANS	5206A-2NS	—	—	24400	17700			
	72	30.2	1.1	5306	—	—	—	—	5306N	5306NR	41500	29000			
35	72	27	1.1	5207	—	—	—	—	5207N	5207NR	40000	29500			
	72	27	1.1	—	5207Z	5207ZZ	5207NS	5207-2NS	—	—	35000	25900			
	72	27	1.1	5207A	—	—	—	—	5207AN	5207ANR	38000	27700			
	72	27	1.1	—	5207AZ	5207AZZ	5207ANS	5207A-2NS	—	—	33000	24500			
	80	34.9	1.5	5307	—	—	—	—	5307N	5307NR	52000	37000			
40	80	30.2	1.1	5208	—	—	—	—	5208N	5208NR	45500	34000			
	80	30.2	1.1	—	5208Z	5208ZZ	5208NS	5208-2NS	—	—	40000	30500			
	80	30.2	1.1	5208A	—	—	—	—	5208AN	5208ANR	42500	32500			
	80	30.2	1.1	—	5208AZ	5208AZZ	5208ANS	5208A-2NS	—	—	37500	28700			
	90	36.5	1.5	5308	—	—	—	—	5308N	5308NR	63500	46500			
45	85	30.2	1.1	5209	—	—	—	—	5209N	5209NR	51000	39000			
	85	30.2	1.1	—	5209Z	5209ZZ	5209NS	5209-2NS	—	—	42500	34500			
	85	30.2	1.1	5209A	—	—	—	—	5209AN	5209ANR	48000	37000			
	85	30.2	1.1	—	5209AZ	5209AZZ	5209ANS	5209A-2NS	—	—	40000	32500			
100	39.7	1.5	5309	—	—	—	—	5309N	5309NR	76500	56500				

備考 輪溝および止め輪の寸法、精度の詳細は39ページ～42ページに示す。