


●鋼からステンレス鋼、アルミまで、高速・高効率加工ができ、高精度穴あけが可能です。

This drill having stub length is useful in material from Carbon Steels and Stainless Steels to Aluminum.



切削条件 Drilling Condition : A-230

LIST 7572P

オーダー方法

SGESS 直径

単位 (Unit) : mm / 円 (¥)

直径 Dc	溝長 l	全長 L	シャンク径 Ds	シャンク長 ls	在庫 Stock	参考価格 Price
1.0	6	38	3	28	●	1,150
1.01	6	38	3	28	●	1,220
1.02	6	38	3	28	●	1,220
1.03	6	38	3	28	●	1,220
1.04	6	38	3	28	●	1,220
1.05	6	38	3	28	●	1,150
1.06	6	38	3	28	●	1,220
1.07	7	39	3	28	●	1,220
1.08	7	39	3	28	●	1,220
1.09	7	39	3	28	●	1,220
1.1	7	39	3	28	●	1,050
1.11	7	39	3	28	●	1,220
1.12	7	39	3	28	●	1,220
1.13	7	39	3	28	●	1,220
1.14	7	39	3	28	●	1,220
1.15	7	39	3	28	●	1,050
1.16	7	39	3	28	●	1,220
1.17	7	39	3	28	●	1,220
1.18	7	39	3	28	●	1,220
1.19	8	40	3	28	●	1,220
1.2	8	40	3	28	●	1,050
1.21	8	40	3	28	●	1,220
1.22	8	40	3	28	●	1,220
1.23	8	40	3	28	●	1,220
1.24	8	40	3	28	●	1,220
1.25	8	40	3	28	●	1,050
1.26	8	40	3	28	●	1,220
1.27	8	40	3	28	●	1,220
1.28	8	40	3	28	●	1,220
1.29	8	40	3	28	●	1,220
1.3	8	40	3	28	●	1,050
1.31	8	40	3	28	●	1,220
1.32	8	40	3	28	●	1,220
1.33	9	41	3	28	●	1,220
1.34	9	41	3	28	●	1,220
1.35	9	41	3	28	●	1,050
1.36	9	41	3	28	●	1,220
1.37	9	41	3	28	●	1,220
1.38	9	41	3	28	●	1,220
1.39	9	41	3	28	●	1,220
1.4	9	41	3	28	●	1,050
1.41	9	41	3	28	●	1,220
1.42	9	41	3	28	●	1,220
1.43	9	41	3	28	●	1,220
1.44	9	41	3	28	●	1,220
1.45	9	41	3	28	●	1,050
1.46	9	41	3	28	●	1,220
1.47	9	41	3	28	●	1,220
1.48	9	41	3	28	●	1,220
1.49	9	41	3	28	●	1,220
1.5	9	41	3	28	●	1,050
1.51	10	42	3	28	●	1,090
1.52	10	42	3	28	●	1,090
1.53	10	42	3	28	●	1,090
1.54	10	42	3	28	●	1,090
1.55	10	42	3	28	●	943
1.56	10	42	3	28	●	1,090
1.57	10	42	3	28	●	1,090
1.58	10	42	3	28	●	1,090
1.59	10	42	3	28	●	1,090

直径 Dc	溝長 l	全長 L	シャンク径 Ds	シャンク長 ls	在庫 Stock	参考価格 Price
1.6	10	42	3	28	●	943
1.61	10	42	3	28	●	1,090
1.62	10	42	3	28	●	1,090
1.63	10	42	3	28	●	1,090
1.64	10	42	3	28	●	1,090
1.65	10	42	3	28	●	943
1.66	10	42	3	28	●	1,090
1.67	10	42	3	28	●	1,090
1.68	10	42	3	28	●	1,090
1.69	10	42	3	28	●	1,090
1.7	10	42	3	28	●	943
1.71	11	43	3	28	●	1,090
1.72	11	43	3	28	●	1,090
1.73	11	43	3	28	●	1,090
1.74	11	43	3	28	●	1,090
1.75	11	43	3	28	●	943
1.76	11	43	3	28	●	1,090
1.77	11	43	3	28	●	1,090
1.78	11	43	3	28	●	1,090
1.79	11	43	3	28	●	1,090
1.8	11	43	3	28	●	943
1.81	11	43	3	28	●	1,090
1.82	11	43	3	28	●	1,090
1.83	11	43	3	28	●	1,090
1.84	11	43	3	28	●	1,090
1.85	11	43	3	28	●	943
1.86	11	43	3	28	●	1,090
1.87	11	43	3	28	●	1,090
1.88	11	43	3	28	●	1,090
1.89	11	43	3	28	●	1,090
1.9	11	43	3	28	●	943
1.91	12	44	3	28	●	1,090
1.92	12	44	3	28	●	1,090
1.93	12	44	3	28	●	1,090
1.94	12	44	3	28	●	1,090
1.95	12	44	3	28	●	943
1.96	12	44	3	28	●	1,090
1.97	12	44	3	28	●	1,090
1.98	12	44	3	28	●	1,090
1.99	12	44	3	28	●	1,090
2.0	12	44	3	28	●	943
2.01	12	44	3	28	●	1,290
2.02	12	44	3	28	●	1,290
2.03	12	44	3	28	●	1,290
2.04	12	44	3	28	●	1,290
2.05	12	44	3	28	●	1,120
2.06	12	44	3	28	●	1,290
2.07	12	44	3	28	●	1,290
2.08	12	44	3	28	●	1,290
2.09	12	44	3	28	●	1,290
2.1	12	44	3	28	●	1,120
2.11	12	44	3	28	●	1,290
2.12	12	44	3	28	●	1,290
2.13	13	45	3	28	●	1,290
2.14	13	45	3	28	●	1,290
2.15	13	45	3	28	●	1,120
2.16	13	45	3	28	●	1,290
2.17	13	45	3	28	●	1,290
2.18	13	45	3	28	●	1,290
2.19	13	45	3	28	●	1,290