


# SAD-LC / SADS-LC Screw Adaptor - Left - handed Threaded Type



WEB Selection Tool

WEB CAD Download

SUS Stainless steel



- By combining with female screw products such as a lever and knob, this may be used as a left-handed screw lever or knob.
- For screw fixing, use a pin stopper or anaerobic adhesive agent. If it is repeatedly tightened, a pin stopper is recommended.
- Use a stopper ring to accurately determine the threaded length.

- Material/Finish ❶ RoHS Compliant

	SAD-LC Made of Steel	SADS-LC Made of Stainless Steel
Thread Part	SUM22 Trivalent Chromate Treatment	SUS303
Stopper Ring	Equivalent to SUS304	Equivalent to SUS304

## Dimensions

Unit : mm

Part Number Steel	Part Number Stainless steel	M (Right-hand screw) <span style="color: red;">❷</span>	M <sub>1</sub> (Left-hand screw)	Lm	s	t	D	Mass (g)
SAD-M4-LC	SADS-M4-LC	M4	M4	4.5	1.4	0.6	7	0.9 - 2.5
SAD-M5-LC	SADS-M5-LC	M5	M5	4.5	1.6	0.6	9	1.5 - 6.3
SAD-M6-LC	SADS-M6-LC	M6	M6	5.5	2	0.6	9	2.2 - 11
SAD-M8-LC	SADS-M8-LC	M8	M8	6.5	2.5	0.8	12	3.9 - 26
SAD-M10-LC	SADS-M10-LC	M10	M10	8.5	3	0.8	16	8.2 - 41

**SAD-LC** Made of Steel **SADS-LC** Made of Stainless Steel

Part Number	L (mm) <span style="color: red;">❸</span>									
	12	16	20	25	32	40	50	63	80	
SAD-M4-LC	●	●	●	●	●					
SAD-M5-LC	●	●	●	●	●	●	●			
SAD-M6-LC	●	●	●	●	●	●	●	●		
SAD-M8-LC	●	●	●	●	●	●	●	●	●	
SAD-M10-LC	●	●	●	●	●	●	●	●	●	
SADS-M4-LC	●	●	●	●	●					
SADS-M5-LC	●	●	●	●	●	●	●			
SADS-M6-LC	●	●	●	●	●	●	●	●		
SADS-M8-LC	●	●	●	●	●	●	●	●	●	
SADS-M10-LC		●	●	●	●	●	●	●	●	

### ● Related Products

Screw adaptor with variable

screw diameter **SAD-SD**

**SADS-SD** are available.

→ P.530



- Part number specification

**SAD-M5-32-LC**

❶ ❷ ❸ Left Threaded Type

Cleanroom Wash & Packaging → P.792

Screw Combination → P.798

Screw Length Adjustment → P.796

Vibration Resistant → P.795

Available / Add'l charge

Available / Add'l charge

Available / Add'l charge

Available / Add'l charge