


SSB-A Stopper Bolt - Tip Sphere Type

Recommendation



WEB Selection Tool

WEB CAD Download



Material/Finish

RoHS Compliant

SSB-A	
Thread Part	S45C, sphere part quenching (hardness: 45 HRC or above) Ferrosoferric Oxide Film (Black)
Nut	SS400 Trivalent Chromate Treatment

- Screw tip is round.
- Round part has already been quenched. It is highly abrasion-resistant.
- All products are provided with lock nut.

Dimensions


Unit : mm

Part Number	M (coarse)	t	L ₂	T	d	R	L ₁	B	C	Mass (g)
SSB-M4-A	M4	3	2.1	3.2	2	3	2.8	7	8.1	2.6 - 5.2
SSB-M5-A	M5	3	2.4	4	3	3	3.5	8	9.2	4.5 - 9.7
SSB-M6-A	M6	3.5	3	5	4.5	4	4	10	11.5	7.2 - 15
SSB-M8-A	M8	5	3.7	6.5	6	5	5.5	13	15	15 - 40
SSB-M10-A	M10	5.5	4.5	8	7	5	7	17	19.6	38 - 63
SSB-M12-A	M12	7	5.2	10	9	8	8	19	21.9	54 - 99
SSB-M16-A	M16	9	6	13	12	10	10	24	27.7	111 - 158

Part Number	L (mm)										
	10	15	20	25	30	35	40	50	60	70	80
SSB-M4-A	●	●	●	●	●	●	●				
SSB-M5-A	●	●	●	●	●	●	●	●			
SSB-M6-A		●	●	●	●	●	●	●			
SSB-M8-A		●	●	●	●	●	●	●	●	●	●
SSB-M10-A					●	●	●	●	●	●	●
SSB-M12-A					●	●	●	●	●	●	●
SSB-M16-A								●	●	●	●

Usage example

Use the lock nut on an opposite side of the side that receives the force.



Related Products

A locating block **[SBN]** is available for stopper bolt mounting.
→ P.537



Part number specification

SSB-M8-40-A

Product Code **1** **2** Tip Sphere Type

Cleanroom Wash & Packaging → P.792

Screw Combination → P.798

Screw Length Adjustment → P.796

Vibration Resistant → P.795

Not Available

Not Available

Not Available

Available / Add'l charge