


SUB Stopper Bolt with Urethane Pad



WEB Selection
Tool

WEB CAD
Download



- For work locating and stopping.
- Urethane pad is adhered.
- Impact is absorbed by the urethane pad.
- All products are provided with lock nut.

• Material/Finish

RoHS Compliant

| | SUB |
|-------------|---------------------------------------|
| Thread Part | SS400 Nickel Plating |
| Pad | Polyurethane (hardness: 90 HDA) |
| Lock Nut | SS400 Trivalent Chromate Treatment |

Dimensions

Unit : mm

| Part Number | M (coarse) | L2 | L1 | D1 | t | h | B | C | T | Mass (g) |
|-------------|------------|----|-----|----|-----|-----|----|------|-----|------------|
| SUB-M4 | M4 | 3 | 2.8 | 5 | 1.5 | 1.5 | 7 | 8.1 | 2.4 | 2.1 - 4.1 |
| SUB-M5 | M5 | 3 | 3.5 | 6 | 1.5 | 1.5 | 8 | 9.2 | 3.2 | 3.3 - 6.6 |
| SUB-M6 | M6 | 3 | 4 | 8 | 2 | 2 | 10 | 11.5 | 3.6 | 6.3 - 11.7 |
| SUB-M8 | M8 | 3 | 5.5 | 10 | 2 | 2 | 13 | 15 | 5 | 12.7 - 23 |
| SUB-M10 | M10 | 3 | 7 | 13 | 2 | 2 | 17 | 19.6 | 6 | 24 - 39 |

| Part Number | L (mm) | | | | | | | |
|-------------|--------|----|----|----|----|----|----|----|
| | 15 | 20 | 25 | 30 | 35 | 40 | 45 | 50 |
| SUB-M4 | ● | ● | ● | ● | ● | ● | | |
| SUB-M5 | ● | ● | ● | ● | ● | ● | | |
| SUB-M6 | | ● | ● | ● | ● | ● | ● | ● |
| SUB-M8 | | ● | ● | ● | ● | ● | ● | ● |
| SUB-M10 | | ● | ● | ● | ● | ● | ● | ● |

- Part number specification

SUB-M4 - 35

Product Code

| | | | |
|------------------------------------|---------------------------|---------------------------------|--------------------------------|
| Cleanroom Wash & Packaging → P.792 | Screw Combination → P.798 | Screw Length Adjustment → P.796 | Vibration Resistant → P.795 |
| Not Available | Not Available | Available / Add'l charge | Please feel free to contact us |