



# 2DLCM

## DLC ミル アルミ用

DLC-mill for Aluminum

- アルミニウム、銅合金専用のエンドミルです。
- アルミのドライ加工ができます。

This is suitable for Dry-milling of Aluminum with DLC coat.



LIST 9330

オーダ方法

2DLCM 外径

切削条件 Milling Condition ▶▶B-240

単位 (Unit) : mm / 円 (¥)

外径 Dc	溝刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
1	3	40	4	●	4,140
1.1	3	40	4	□	-
1.2	3	40	4	□	-
1.3	3	40	4	□	-
1.4	3	40	4	□	-
1.5	4	40	4	●	4,140
1.6	4	40	4	□	-
1.7	4	40	4	□	-
1.8	5	40	4	□	-
1.9	5	40	4	□	-
2	6	40	4	●	4,090
2.1	6	40	4	□	-
2.2	6	40	4	□	-
2.3	6	40	4	□	-
2.4	8	40	4	□	-
2.5	8	40	4	●	4,090
2.6	8	40	4	□	-
2.7	8	40	4	□	-
2.8	8	40	4	□	-
2.9	8	40	4	□	-
3	8	45	6	●	4,090
3.1	8	45	6	□	-
3.2	8	45	6	□	-
3.3	8	45	6	□	-
3.4	10	45	6	□	-
3.5	10	45	6	●	5,140
3.6	10	45	6	□	-
3.7	10	45	6	□	-
3.8	11	45	6	□	-
3.9	11	45	6	□	-
4	11	45	6	●	5,140
4.1	11	45	6	□	-
4.2	11	45	6	□	-
4.3	11	45	6	□	-
4.4	11	45	6	□	-
4.5	11	50	6	●	5,540
4.6	11	50	6	□	-
4.7	11	50	6	□	-
4.8	13	50	6	□	-
4.9	13	50	6	□	-
5	13	50	6	●	5,540
5.1	13	50	6	□	-
5.2	13	50	6	□	-
5.3	13	50	6	□	-
5.4	13	50	6	□	-
5.5	13	50	6	●	6,270
5.6	13	50	6	□	-
5.7	13	50	6	□	-
5.8	13	50	6	□	-
5.9	13	50	6	□	-
6	13	50	6	●	5,750
6.1	16	60	8	□	-
6.2	16	60	8	□	-
6.3	16	60	8	□	-
6.4	16	60	8	□	-
6.5	16	60	8	□	-
6.6	16	60	8	□	-
6.7	16	60	8	□	-
6.8	16	60	8	□	-
6.9	16	60	8	□	-

外径 Dc	溝刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
7	16	60	8	●	6,860
7.1	16	60	8	□	-
7.2	16	60	8	□	-
7.3	16	60	8	□	-
7.4	16	60	8	□	-
7.5	16	60	8	□	-
7.6	19	60	8	□	-
7.7	19	60	8	□	-
7.8	19	60	8	□	-
7.9	19	60	8	□	-
8	19	60	8	●	7,450
8.1	19	70	10	□	-
8.2	19	70	10	□	-
8.3	19	70	10	□	-
8.4	19	70	10	□	-
8.5	19	70	10	□	-
8.6	19	70	10	□	-
8.7	19	70	10	□	-
8.8	19	70	10	□	-
8.9	19	70	10	□	-
9	19	70	10	●	9,490
9.1	19	70	10	□	-
9.2	19	70	10	□	-
9.3	19	70	10	□	-
9.4	19	70	10	□	-
9.5	19	70	10	□	-
9.6	22	70	10	□	-
9.7	22	70	10	□	-
9.8	22	70	10	□	-
9.9	22	70	10	□	-
10	22	70	10	●	9,260
10.1	22	75	12	□	-
10.2	22	75	12	□	-
10.3	22	75	12	□	-
10.4	22	75	12	□	-
10.5	22	75	12	□	-
10.6	22	75	12	□	-
10.7	22	75	12	□	-
10.8	22	75	12	□	-
10.9	22	75	12	□	-
11	22	75	12	●	12,200
11.1	22	75	12	□	-
11.2	22	75	12	□	-
11.3	22	75	12	□	-
11.4	22	75	12	□	-
11.5	22	75	12	□	-
11.6	26	75	12	□	-
11.7	26	75	12	□	-
11.8	26	75	12	□	-
11.9	26	75	12	□	-
12	26	75	12	●	12,600
16	32	90	16	●	23,700
20	38	100	20	●	40,000

□は特定代理店在庫品です。  
Available for Japan customers only.