


# 2NAC

## ナタック 2枚刃

NATAC End Mills Two Flutes

●鋼からステンレス鋼、アルミまで加工できる汎用エンドミルです。

This is general end mill for grooving.



LIST 6272

オーダ方法

2NAC 外径

切削条件 Milling Condition ▶▶B-274

単位 (Unit) : mm / 円 (¥)

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stack	参考価格 Price
1	2	50	6	●	2,520
1.1	2.5	50	6	●	3,300
1.2	2.5	50	6	●	3,300
1.3	3	50	6	●	3,300
1.4	3	50	6	●	3,300
1.5	3	50	6	●	2,300
1.6	3.5	50	6	●	3,010
1.7	3.5	50	6	●	3,010
1.8	4	50	6	●	3,010
1.9	4	50	6	●	3,010
2	4	50	6	●	2,180
2.1	4.5	50	6	●	2,880
2.2	4.5	50	6	●	2,880
2.3	5	50	6	●	2,880
2.4	5	50	6	●	2,880
2.5	5	50	6	●	2,150
2.6	5.5	50	6	●	2,840
2.7	5.5	50	6	●	2,840
2.8	6	50	6	●	2,840
2.9	6	50	6	●	2,840
3	6	50	6	●	1,900
3.1	6.5	50	6	●	2,470
3.2	6.5	50	6	●	2,470
3.3	7	50	6	●	2,470
3.4	7	50	6	●	2,470
3.5	8	60	8	●	1,900
3.6	8	60	8	●	2,470
3.7	8	60	8	●	2,470
3.8	8	60	8	●	2,470
3.9	8	60	8	●	2,470
4	8	60	8	●	1,900
4.1	9	60	8	●	2,470
4.2	9	60	8	●	2,470
4.3	10	60	8	●	2,470
4.4	10	60	8	●	2,470
4.5	10	60	8	●	1,900
4.6	10	60	8	●	2,470
4.7	10	60	8	●	2,470
4.8	10	60	8	●	2,470
4.9	10	60	8	●	2,470
5	10	60	8	●	1,900
5.1	12	60	8	●	2,470
5.2	12	60	8	●	2,470
5.3	12	60	8	●	2,470
5.4	12	60	8	●	2,470
5.5	12	60	8	●	1,900
5.6	12	60	8	●	2,470
5.7	12	60	8	●	2,470
5.8	12	60	8	●	2,470
5.9	12	60	8	●	2,470
6	12	60	8	●	1,900
6.1	14	65	8	●	2,720
6.2	14	65	8	●	2,720
6.3	14	65	8	●	2,720
6.4	14	65	8	●	2,720
6.5	14	65	10	●	2,080
6.6	14	65	10	●	2,720
6.7	14	65	10	●	2,720
6.8	14	65	10	●	2,720
6.9	14	65	10	●	2,720

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stack	参考価格 Price
7	14	65	10	●	2,080
7.1	14	65	10	●	2,720
7.2	14	65	10	●	2,720
7.3	14	65	10	●	2,720
7.4	14	65	10	●	2,720
7.5	14	65	10	●	2,080
7.6	14	65	10	●	2,720
7.7	14	65	10	●	2,720
7.8	14	65	10	●	2,720
7.9	14	65	10	●	2,720
8	14	65	10	●	2,080
8.1	18	70	10	●	3,140
8.2	18	70	10	●	3,140
8.3	18	70	10	●	3,140
8.4	18	70	10	●	3,140
8.5	18	70	10	●	2,410
8.6	18	70	10	●	3,140
8.7	18	70	10	●	3,140
8.8	18	70	10	●	3,140
8.9	18	70	10	●	3,140
9	18	70	10	●	2,410
9.1	18	70	10	●	3,140
9.2	18	70	10	●	3,140
9.3	18	70	10	●	3,140
9.4	18	70	10	●	3,140
9.5	18	70	10	●	2,410
9.6	18	70	10	●	3,140
9.7	18	70	10	●	3,140
9.8	18	70	10	●	3,140
9.9	18	70	10	●	3,140
10	18	70	10	●	2,410
10.1	22	80	12	●	4,030
10.2	22	80	12	●	4,030
10.3	22	80	12	●	4,030
10.4	22	80	12	●	4,030
10.5	22	80	12	●	4,030
10.6	22	80	12	●	4,030
10.7	22	80	12	●	4,030
10.8	22	80	12	●	4,030
10.9	22	80	12	●	4,030
11	22	80	12	●	3,110
11.1	22	80	12	●	4,030
11.2	22	80	12	●	4,030
11.3	22	80	12	●	4,030
11.4	22	80	12	●	4,030
11.5	22	80	12	●	4,030
11.6	22	80	12	●	4,030
11.7	22	80	12	●	4,030
11.8	22	80	12	●	4,030
11.9	22	80	12	●	4,030
12	22	80	12	●	3,110
12.1	26	90	16	●	5,000
12.2	26	90	16	●	5,000
12.3	26	90	16	●	5,000
12.4	26	90	16	●	5,000
12.5	26	90	16	●	5,000
12.6	26	90	16	●	5,000
12.7	26	90	16	●	5,000
12.8	26	90	16	●	5,000
12.9	26	90	16	●	5,000

総目次

Non Coat

刃先  
スクエア

ラジアス  
R

ボール  
R

刃数  
2枚刃

3枚刃

4枚刃

6枚刃  
~

刃長

ショート  
~1.5D

レギュラー  
2D

ミディアム  
3D

ロング

ロングネック  
ロングシャンク

粗・  
中仕上

高硬度

アルミ・  
非鉄金属