


2SE

スーパーハード 2枚刃

SUPER HARD End Mills Two Flutes

●鋼からステンレス鋼、アルミまで加工できる汎用エンドミルです。

This is general end mill for grooving.



LIST 6230

オーダ方法

2SE 外径 *印商品のオーダ方法 2SE 外径 × シャンク径

切削条件 Milling Condition ▶▶B-274

単位 (Unit) : mm / 円 (¥)

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
1	2	50	6	●	2,520
1.5	3	50	6	●	2,300
2	7	50	6	●	2,180
2.5	7	50	6	●	2,150
3	9	50	6	●	1,900
3.5	12	60	8	●	1,900
4	12	60	8	●	1,900
4.5	15	60	8	●	1,900
5	15	60	8	●	1,900
5.5	15	60	8	●	1,900
6	15	60	8	●	1,900
6.5	20	65	10	●	2,080
7	20	65	10	●	2,080
7.5	20	65	10	●	2,080
8	20	65	10	●	2,080
8.5	25	75	10	●	2,410
9	25	75	10	●	2,410
9.5	25	75	10	●	2,410
10	25	75	10	●	2,410
11	30	80	12	●	3,110
12	30	80	12	●	3,110
13	35	90	16	●	3,830
14	35	90	16	●	3,830
15	40	95	16	●	4,280
16	40	95	16	●	4,610
17	40	105	20	●	5,530
18	40	105	20	●	5,530
19	45	110	20	●	6,630
20	45	110	20	●	6,630
20.1	45	110	20	□	-
20.2	45	110	20	□	-
20.3	45	110	20	□	-
20.4	45	110	20	□	-
20.5	45	110	20	□	-
20.6	45	110	20	□	-
20.7	45	110	20	□	-
20.8	45	110	20	□	-
20.9	45	110	20	□	-
21	45	110	20	●	8,020
21.1	45	110	20	□	-
21.2	45	110	20	□	-
21.3	45	110	20	□	-
21.4	45	110	20	□	-
21.5	45	110	20	□	-
21.6	45	110	20	□	-
21.7	45	110	20	□	-
21.8	45	110	20	□	-
21.9	45	110	20	□	-
22	45	110	20	●	8,020
22.1	50	120	25	□	-
22.2	50	120	25	□	-
22.3	50	120	25	□	-
22.4	50	120	25	□	-
22.5	50	120	25	□	-
22.6	50	120	25	□	-
22.7	50	120	25	□	-
22.8	50	120	25	□	-
22.9	50	120	25	□	-
23	50	120	25	●	9,280
23.1	50	120	25	□	-

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
23.2	50	120	25	□	-
23.3	50	120	25	□	-
23.4	50	120	25	□	-
23.5	50	120	25	□	-
23.6	50	120	25	□	-
23.7	50	120	25	□	-
23.8	50	120	25	□	-
23.9	50	120	25	□	-
24	50	120	25	●	9,280
24.1	50	120	25	□	-
24.2	50	120	25	□	-
24.3	50	120	25	□	-
24.4	50	120	25	□	-
24.5	50	120	25	□	-
24.6	50	120	25	□	-
24.7	50	120	25	□	-
24.8	50	120	25	□	-
24.9	50	120	25	□	-
25	50	120	25	●	9,280
25.1	50	120	25	□	-
25.2	50	120	25	□	-
25.3	50	120	25	□	-
25.4	50	120	25	□	-
25.5	50	120	25	□	-
25.6	50	120	25	□	-
25.7	50	120	25	□	-
25.8	50	120	25	□	-
25.9	50	120	25	□	-
26	50	120	25	●	9,890
26.1	55	125	25	□	-
26.2	55	125	25	□	-
26.3	55	125	25	□	-
26.4	55	125	25	□	-
26.5	55	125	25	□	-
26.6	55	125	25	□	-
26.7	55	125	25	□	-
26.8	55	125	25	□	-
26.9	55	125	25	□	-
27	55	125	25	●	11,900
27.1	55	125	25	□	-
27.2	55	125	25	□	-
27.3	55	125	25	□	-
27.4	55	125	25	□	-
27.5	55	125	25	□	-
27.6	55	125	25	□	-
27.7	55	125	25	□	-
27.8	55	125	25	□	-
27.9	55	125	25	□	-
28	55	125	25	●	11,900
28.1	55	125	25	□	-
28.2	55	125	25	□	-
28.3	55	125	25	□	-
28.4	55	125	25	□	-
28.5	55	125	25	□	-
28.6	55	125	25	□	-
28.7	55	125	25	□	-
28.8	55	125	25	□	-
28.9	55	125	25	□	-
29	55	125	25	●	14,500
29.1	55	125	25	□	-

総目次

Non Coat

刃先 スクエア

ラジアス (r)

ボール (R)

刃数 2枚刃

3枚刃

4枚刃

6枚刃 ~

刃長

ショート ~1.5D

レギュラー 2D

ミディアム 3D

ロング

ロングネック
ロングシャンク

粗・中仕上げ

高硬度

アルミ・非鉄金属