


●アルミ合金の深穴の高効率加工が可能です。

This drill is suitable for the high efficiency and deep hole drilling in Aluminum Alloy.



オーダ方法

DLCPLSD 直径 × 全長

単位 (Unit) : mm

| 直径 Dc | 全長 L | 溝長 ℓ | 在庫 Stock |
|-------|------|------|----------|
| 1.0 | 56 | 33 | |
| 1.0 | 100 | 60 | |
| 1.1 | 60 | 37 | |
| 1.1 | 100 | 60 | |
| 1.2 | 65 | 41 | |
| 1.2 | 105 | 65 | |
| 1.3 | 65 | 41 | |
| 1.3 | 105 | 65 | |
| 1.4 | 70 | 45 | |
| 1.4 | 110 | 70 | |
| 1.5 | 70 | 45 | |
| 1.5 | 110 | 70 | |
| 1.6 | 76 | 50 | |
| 1.6 | 115 | 75 | |
| 1.7 | 76 | 50 | |
| 1.7 | 115 | 75 | |
| 1.8 | 80 | 53 | |
| 1.8 | 120 | 80 | |
| 1.9 | 80 | 53 | |
| 1.9 | 120 | 80 | |
| 2.0 | 85 | 56 | |
| 2.0 | 125 | 85 | |
| 2.1 | 85 | 56 | |
| 2.1 | 125 | 85 | |
| 2.2 | 90 | 59 | |
| 2.2 | 135 | 90 | |
| 2.3 | 90 | 59 | |
| 2.3 | 135 | 90 | |
| 2.4 | 95 | 62 | |
| 2.4 | 140 | 95 | |
| 2.5 | 95 | 62 | □ |
| 2.5 | 140 | 95 | |
| 2.6 | 95 | 62 | |
| 2.6 | 140 | 95 | |
| 2.7 | 100 | 66 | |
| 2.7 | 150 | 100 | |
| 2.8 | 100 | 66 | |
| 2.8 | 150 | 100 | |
| 2.9 | 100 | 66 | |
| 2.9 | 150 | 100 | |
| 3.0 | 100 | 66 | |
| 3.0 | 150 | 100 | |
| 3.1 | 106 | 69 | |
| 3.1 | 155 | 105 | |
| 3.2 | 106 | 69 | |
| 3.2 | 155 | 105 | |
| 3.3 | 106 | 69 | |
| 3.3 | 155 | 105 | |
| 3.4 | 112 | 73 | |
| 3.4 | 165 | 115 | |
| 3.5 | 112 | 73 | |
| 3.5 | 165 | 115 | |
| 3.6 | 112 | 73 | |
| 3.6 | 165 | 115 | |
| 3.7 | 112 | 73 | |
| 3.7 | 165 | 115 | |
| 3.8 | 119 | 78 | |
| 3.8 | 175 | 120 | |
| 3.9 | 119 | 78 | |
| 3.9 | 175 | 120 | |
| 4.0 | 119 | 78 | |

| 直径 Dc | 全長 L | 溝長 ℓ | 在庫 Stock |
|-------|------|------|----------|
| 4.0 | 175 | 120 | |
| 4.1 | 119 | 78 | |
| 4.1 | 175 | 120 | |
| 4.2 | 119 | 78 | |
| 4.2 | 175 | 120 | |
| 4.3 | 126 | 82 | |
| 4.3 | 185 | 125 | |
| 4.4 | 126 | 82 | |
| 4.4 | 185 | 125 | |
| 4.5 | 126 | 82 | |
| 4.5 | 185 | 125 | |
| 4.6 | 126 | 82 | |
| 4.6 | 185 | 125 | |
| 4.7 | 126 | 82 | |
| 4.7 | 185 | 125 | |
| 4.8 | 132 | 87 | |
| 4.8 | 195 | 135 | |
| 4.9 | 132 | 87 | |
| 4.9 | 195 | 135 | |
| 5.0 | 132 | 87 | |
| 5.0 | 195 | 135 | |
| 5.1 | 132 | 87 | |
| 5.1 | 195 | 135 | |
| 5.2 | 132 | 87 | |
| 5.2 | 195 | 135 | |
| 5.3 | 132 | 87 | |
| 5.3 | 195 | 135 | |
| 5.4 | 139 | 91 | |
| 5.4 | 205 | 140 | |
| 5.5 | 139 | 91 | |
| 5.5 | 205 | 140 | |
| 5.6 | 139 | 91 | |
| 5.6 | 205 | 140 | |
| 5.7 | 139 | 91 | |
| 5.7 | 205 | 140 | |
| 5.8 | 139 | 91 | |
| 5.8 | 205 | 140 | |
| 5.9 | 139 | 91 | |
| 5.9 | 205 | 140 | |
| 6.0 | 139 | 91 | |
| 6.0 | 205 | 140 | |
| 6.1 | 148 | 97 | |
| 6.1 | 215 | 150 | |
| 6.2 | 148 | 97 | |
| 6.2 | 215 | 150 | |
| 6.3 | 148 | 97 | |
| 6.3 | 215 | 150 | |
| 6.4 | 148 | 97 | |
| 6.4 | 215 | 150 | |
| 6.5 | 148 | 97 | |
| 6.5 | 215 | 150 | |
| 6.6 | 148 | 97 | |
| 6.6 | 215 | 150 | |
| 6.7 | 148 | 97 | |
| 6.7 | 215 | 150 | |
| 6.8 | 156 | 102 | |
| 6.8 | 225 | 155 | |
| 6.9 | 156 | 102 | |
| 6.9 | 225 | 155 | |
| 7.0 | 156 | 102 | |
| 7.0 | 225 | 155 | |

□は特定代理店在庫品です。
 □: Available for Japan customers only.

次頁

シャンク部の径はドリル直径よりもマイナスに仕上げられています。溝長の長いドリルでは大きなマイナスとなるために、ドリルコレットをご使用の場合には、締め代に余裕があるコレットを選定ください。詳細は G-8 を参照ください。

