


AGSUSS

AG-SUS ドリルショート

AG-SUS Drills Short

●ステンレス鋼に最適なドリルです。耐熱性に優れたAGコートにより安定した穴加工ができます。

This drill meets stable drilling by AG coat, and is very suitable for drilling of Stainless Steel.



切削条件 Drilling Condition **A-229**

LIST 6596P

オーダー方法

AGSUSS 直径

単位 (Unit) : mm / 円 (¥)

直径 Dc	溝長 l	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
0.5	3	38	3	□	-
0.51	3	38	3	□	-
0.52	3	38	3	□	-
0.53	3	38	3	□	-
0.54	3	38	3	□	-
0.55	3	38	3	□	-
0.56	3	38	3	□	-
0.57	3	38	3	□	-
0.58	3	38	3	□	-
0.59	3	38	3	□	-
0.6	3.5	38	3	□	-
0.61	3.5	38	3	□	-
0.62	3.5	38	3	□	-
0.63	3.5	38	3	□	-
0.64	3.5	38	3	□	-
0.65	3.5	38	3	□	-
0.66	3.5	38	3	□	-
0.67	3.5	38	3	□	-
0.68	3.5	38	3	□	-
0.69	3.5	38	3	□	-
0.7	4.5	38	3	□	-
0.71	4.5	38	3	□	-
0.72	4.5	38	3	□	-
0.73	4.5	38	3	□	-
0.74	4.5	38	3	□	-
0.75	4.5	38	3	□	-
0.76	4.5	38	3	□	-
0.77	4.5	38	3	□	-
0.78	4.5	38	3	□	-
0.79	4.5	38	3	□	-
0.8	5	38	3	□	-
0.81	5	38	3	□	-
0.82	5	38	3	□	-
0.83	5	38	3	□	-
0.84	5	38	3	□	-
0.85	5	38	3	□	-
0.86	5	38	3	□	-
0.87	5	38	3	□	-
0.88	5	38	3	□	-
0.89	5	38	3	□	-
0.9	5.5	38	3	□	-
0.91	5.5	38	3	□	-
0.92	5.5	38	3	□	-
0.93	5.5	38	3	□	-
0.94	5.5	38	3	□	-
0.95	5.5	38	3	□	-
0.96	5.5	38	3	□	-
0.97	5.5	38	3	□	-
0.98	5.5	38	3	□	-
0.99	5.5	38	3	□	-
1.0	6	40	3	●	701
1.01	6	40	3	●	940
1.02	6	40	3	●	940
1.03	6	40	3	●	940
1.04	6	40	3	●	940
1.05	6	40	3	●	856
1.06	6	40	3	●	940
1.07	7	40	3	●	940
1.08	7	40	3	●	940
1.09	7	40	3	●	940

直径 Dc	溝長 l	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
1.1	7	40	3	●	816
1.11	7	40	3	●	940
1.12	7	40	3	●	940
1.13	7	40	3	●	940
1.14	7	40	3	●	940
1.15	7	40	3	●	856
1.16	7	40	3	●	940
1.17	7	40	3	●	940
1.18	7	40	3	●	940
1.19	8	40	3	●	940
1.2	8	40	3	●	816
1.21	8	40	3	●	940
1.22	8	40	3	●	940
1.23	8	40	3	●	940
1.24	8	40	3	●	940
1.25	8	40	3	●	856
1.26	8	40	3	●	940
1.27	8	40	3	●	940
1.28	8	40	3	●	940
1.29	8	40	3	●	940
1.3	8	40	3	●	816
1.31	8	40	3	●	940
1.32	8	40	3	●	940
1.33	9	40	3	●	940
1.34	9	40	3	●	940
1.35	9	40	3	●	856
1.36	9	40	3	●	940
1.37	9	40	3	●	940
1.38	9	40	3	●	940
1.39	9	40	3	●	940
1.4	9	40	3	●	816
1.41	9	40	3	●	940
1.42	9	40	3	●	940
1.43	9	40	3	●	940
1.44	9	40	3	●	940
1.45	9	40	3	●	856
1.46	9	40	3	●	940
1.47	9	40	3	●	940
1.48	9	40	3	●	940
1.49	9	40	3	●	940
1.5	9	40	3	●	693
1.51	10	44	3	●	940
1.52	10	44	3	●	940
1.53	10	44	3	●	940
1.54	10	44	3	●	940
1.55	10	44	3	●	856
1.56	10	44	3	●	940
1.57	10	44	3	●	940
1.58	10	44	3	●	940
1.59	10	44	3	●	940
1.6	10	44	3	●	750
1.61	10	44	3	●	940
1.62	10	44	3	●	940
1.63	10	44	3	●	940
1.64	10	44	3	●	940
1.65	10	44	3	●	856
1.66	10	44	3	●	940
1.67	10	44	3	●	940
1.68	10	44	3	●	940
1.69	10	44	3	●	940

食付性のよい先研ぎ形状のため、状況に応じてセンチもみを省略することもできます。切れ味重視の高精度ドリルです。剛性のない機械・ワーククランプなどが低剛性の使用には **AGESS(A-64)** がおすすめです。