


RENY/FH

ガラス繊維強化ポリアミドMXD6 / (+) サラ小ネジ
Glass-fiber-reinforced polyamideMXD6 / Cross recessed flat head screw




品番 Product number		RENY/FH-M○-L○							
M	M2	M2.6	M3	M4	M5	M6	M8		
ピッチ / Pitch	0.4	0.45	0.5	0.7	0.8	1	1.25		
D	4	5.2	6	8	10	12	16		
L	4	—	1,000	—	—	—	—		
	5	—	—	1,000	—	—	—		
	6	1,000	1,000	1,000	1,000	—	—		
	8	1,000	1,000	1,000	1,000	—	—		
	10	1,000	1,000	1,000	1,000	1,000	500	—	
	12	—	1,000	1,000	1,000	1,000	500	—	
	15	—	—	1,000	1,000	500	500	250	
	20	—	—	1,000	1,000	500	250	200	
	25	—	—	1,000	500	500	250	200	
30	—	—	—	—	—	250	100		

販売単位 Quantity

RENY/TPH

ガラス繊維強化ポリアミドMXD6 / (+) ナベタッピンネジ
Glass-fiber-reinforced polyamideMXD6 / Tapping screw




品番 Product number		RENY/TPH-M○-L○							
M	M3	M4							
D×H	5.5×2	7×2.6							
L	8	1,000	1,000						
	10	1,000	1,000						

販売単位 Quantity

RENY/BT

ガラス繊維強化ポリアミドMXD6 / 六角ボルト
Glass-fiber-reinforced polyamideMXD6 / Hexagon head bolt



品番 Product number		RENY/BT-M○-L○									
M	M5	M6	M6	M8	M8	M10	M10	M12	M12	M16	
ピッチ / Pitch	0.8	1	1	1.25	1.25	1.5	1.5	1.75	1.75	2	
B×H	8×3.5	10×4	10×5	13×5.5	13×6	17×7	17×8	19×8	19×10	24×13	
L	8	1,000	—	—	—	—	—	—	—	—	
	10	1,000	500	—	250	—	—	—	—	—	
	12	1,000	500	—	250	—	100	—	—	—	
	15	500	500	—	200	—	100	—	—	—	
	20	500	250	—	200	—	100	—	50	—	
	25	250	250	—	100	—	100	—	50	—	
	30	250	250	—	100	—	50	—	50	—	
	35	250	200	—	100	—	50	—	—	—	
	40	—	200	—	100	—	50	—	50	—	
	45	—	—	—	—	—	50	—	50	—	
	50	—	100	—	50	—	50	—	50	50	
	55	—	—	100	—	50	—	—	—	50	
	60	—	—	100	—	50	—	50	50	50	
	65	—	—	100	—	50	—	—	—	—	
	70	—	—	100	—	50	—	50	50	50	
	75	—	—	100	—	50	—	50	—	—	
80	—	—	100	—	50	—	50	—	50		
90	—	—	100	—	50	—	—	—	—		
100	—	—	50	—	50	—	50	50	50		
120	—	—	—	—	50	—	—	50	—		
150	—	—	—	—	50	—	50	—	50		

表中のカラー部分は、半ネジとなります。M8-50は半ネジ(S=30)、M10-45は半ネジ(S=20)、M10-50は半ネジ(S=25)となります。M6-55~100、M8-55~150、M10-60~150、M16-55~150は半ネジ(S=50)、M12-100~150は半ネジ(S=90)となります。
Colored portion in the table indicates partially threaded screw. M8-50(S=30), M10-45(S=20), M10-50(S=25) and M6-55 to 100, M8-55 to 150, M10-60 to 150, M16-55 to 150 are half screws (S=50), and M12-100 to 150 is half screw (S=90).

販売単位 Quantity