

スラストワッシャー

Thrust washer

ORDER▶品番・サイズ・販売単位にてご注文ください

RoHS
compliant


マイクロねじ	NEW
PC	
PPS	
RENY	
PEEK	
PVC	
PI	
PP	
PTFE	
PFA	
PVDF	
CERAMIC	
ワッシャー	
ローレットねじ	
特殊ボルト&特殊ナット	
スペーサー	
リベット&アンカー	
ブッシュ	
結束バンド	
C型止輪	
プラボネ	
オプションサービス	

項目 / Item	単位 / Unit	ポリソール / Polysoul	ポリスライダー / Polyslider
引張強さ / Tensile strength	kgf/cm	1,400~1,800	1,000
伸び / Extension	%	50~80	60
摩擦係数 / Coefficient of friction	μ	0.02~0.20	0.16~0.40
PV限界値 / PV threshold limit	kgf/cm ² ·m/min	10,000	300
絶縁耐力 / Dielectric strength	KV/m	66.7	45

- 表中の数値は参考値であり保証値ではありません。
- 耐熱性、耐薬品性は使用条件により変化しますので、必ず事前に使用状態でのテストを行ってください。
- ロット、各種条件により若干変色することがあります。
- 在庫サイズ、形状及び使用材料メーカーは予告なく変更することがあります。
- Values in the table are for reference purpose only, and they are not guaranteed values.
- Since heat resistance and chemical resistance changes according to use conditions, ensure to test under actual use conditions beforehand.
- Discoloration to some extent may occur depending on lot and various conditions.
- Size available in stock, configuration and manufacturers of raw materials used may change without any notice.

PO/W


ポリソール／ワッシャー
Polysoul / Washer



品番
Product number **PO/W- d - D - t**

軸径 / Shaft diameter	3	4	5	6			
$d \times D$	3.1×5.4	4.1×6.5	5.2×8	6.2×9.5			
t	0.3	0.3	0.3	0.3			

販売単位 Quantity 1,000 1,000 1,000 1,000



PS/W

ポリスライダー／ワッシャー
Polyslider / Washer



品番
Product number **PS/W- d - D - t**

軸径 / Shaft diameter	1.6	2	2.5	3	3.5	4	4.5	5
$d \times D$	1.6×3.2	2.1×4	2.6×4.7	3.1×5.4	3.6×6	4.1×6.5	4.6×7.2	5.2×8
t	0.13 / 0.25 / 0.5							

販売単位 Quantity 1,000 1,000 1,000 1,000 1,000 1,000 1,000 1,000

軸径 / Shaft diameter	6	7	8	10	12	15
$d \times D$	6.2×9.5	7.2×11	8.2×12	10.2×15	12.2×18	15.2×23
t	0.13 / 0.25 / 0.5					

販売単位 Quantity 1,000 1,000 1,000 1,000 1,000 1,000

上記以外のサイズも製作可能ですので、ご相談ください。
Please free to contact us as we can handle sizes other than those mentioned above.

