


CDS-15

※CDS-100 can become B type(hook type) by replacing the main scale

DIMENSIONS



Units : mm

Model No.	A	B	C	D	E	F	G	H
CDS-15	231	100	51	4	27.5	10.5	2.8	6.1
CDS-20	280	100	51	4	27.5	10.5	2.8	6.1
CDS-30	380	150	47.5	5	30	13	2.8	6.1
CDS-50	590	250	80	10	36	20	5	13.5
CDS-60	690	250	80	10	36	20	5	13.5
CDS-100	1100	250	80	10	36	20	5	13.5

USE • For measuring depth

FEATURES

- Fully hardened measuring faces
- Made of stainless steel(Satin finish)


Order No.	Model No.	Measuring Range (mm)	Graduation (mm)	Accuracy (mm)	Weight
007711	CDS-15	150	0.05	± 0.08	125g
007712	CDS-20	200	0.05	± 0.08	140g
007713	CDS-30	300	0.05	± 0.10	220g
007714	CDS-50	500	0.05	± 0.10	3kg
007715	CDS-60	600	0.05	± 0.12	3kg
007716	CDS-100	1000	0.05	± 0.15	4kg

DIGITAL MINI DEPTH GAUGES



DIMENSIONS

Units : mm



USE • For measuring depth

FEATURES

- With hold display function
- Auto display off function (after 5 min.)
- One CR2032 (Lithium) battery included for testing

Order No.	Model No.	Measuring Range (mm)	Resolution (mm)	Accuracy* (mm)	Weight
151195	DMD-25G	0-25	0.1	± 0.2	40g

※ Quantization Error (± 1 digit) not included