




**MCD233-25FA**

## DIMENSIONS



Units: mm

Model No.	A	B	C	D	E
MCD233-25FA	63	9	4.5	18	17
MCD233-25FB	101.5	9	4.5	18	17

- USE**
  - For depth measurement
- FEATURES**
  - $\phi$  4.5mm measuring rod
  - High carbon chrome steel
  - Quick display of the measured value
  - With ratchet stop
  - Auto display off function (after 5 min.)
  - One SR44 (Silver oxide) battery included for testing

Order No.	Model No.	Measuring Range (mm)	Resolution (mm)	Maximum Error* ( $\mu$ m)	Weight
152181	MCD233-25FA	0-25	0.001	6	310g
152182	MCD233-25FB	0-25	0.001	6	380g


\* Quantization Error ( $\pm 1$  digit) not included

# DEPTH MICROMETERS



**MC202-25F**

## DIMENSIONS



Units: mm

Model No.	A	B	C	D	E
MC202-25F	63	9	4.5	18	17
MC202-25FS	101.5	9	4.5	18	17

- USE**
  - For depth measurement
- FEATURES**
  - $\phi$  4.5mm measuring rod
  - High carbon chrome steel
  - With ratchet stop



Order No.	Model No.	Measuring Range (mm)	Graduation (mm)	Maximum Error ( $\mu$ m)	Weight
151220	MC202-25F	0 ~ 25	0.01	4	210g
151221	MC202-25FS	0 ~ 25	0.01	4	265g