





AI TYPE




測定例




BI TYPE



Measurement Example



DIMENSIONS



- ① PUSH BUTTON
- ② MOVING ARM
- ③ FIXED ARM
- ④ BEZEL (RING)
- ⑤ LIMIT INDICATOR
- ⑥ CLAMP

Units : mm

Model No.	Leg Length	A	B	C	D	E
AI-0	40	2.3	1.1	2.8	1.1	2.8
AI-1	40	2.3	1.1	2.8	1.1	2.8
AI-2	40	2.3	2.7	4.5	2.3	4.8
AI-3	40	2.3	8	11	4.4	6.7
AI-4	40	2.3	18	21	4.4	6.7
AI-5	40	2.3	28	31	4.4	6.7
BI-0	80	Tip 0.5	7	9	7	9
BI-1	80	2.3	2.6	4.6	2.6	4.6
BI-2	80	2.3	5.1	7.1	4.8	6.8
BI-3	80	2.3	7.5	10	8.6	10.6
BI-4	80	2.3	17.5	20	8.6	10.6
BI-5	80	2.3	27.5	30	8.6	10.6

USE

- For measuring bore size

MATERIAL

- Body : Steel

※ Custom shape product available by special order

Order No.	Model No.	Graduation (mm)	Measuring Range (mm)	Accuracy (mm)
151540	AI-0	0.01	3~ 9	±0.05
151541	AI-1	0.01	6~18	±0.05
151542	AI-2	0.01	10~22	±0.05
151543	AI-3	0.01	20~32	±0.05
151544	AI-4	0.01	30~42	±0.05
151545	AI-5	0.01	40~52	±0.05
151550	BI-0	0.02	10~34	±0.05
151551	BI-1	0.025	10~35	±0.05
151552	BI-2	0.025	20~45	±0.05
151553	BI-3	0.025	30~55	±0.05
151554	BI-4	0.025	40~65	±0.05
151555	BI-5	0.025	50~75	±0.05

DIAL GAUGES

DIAL GAUGES

DIAL INDICATORS

THICKNESS GAUGES

BORE GAUGES

CALIPER GAUGES

HARDNESS-TENSION GAUGE

MAGNETIC BASE