


PRECISION LEVEL (JIS CLASS A)




- USE**
- Bubble tube indicates horizontal and measures small inclinations
 - Precision measurement for machine inspection and leveling

FEATURES

- JIS B7510 standard product
- Special tool steel body (hardened) is lapped and polished
- Sensitivity : 0.02mm/m
- Accuracy of the main bubble Full range accuracy : less than ± 0.5 graduation
Adjacent accuracy : less than 0.2 graduation
- Parallelism between V groove and base : within 0.5 graduation
- Parallelism on base : within 0.003mm

Order No.	Model No.	Standard (mm)	Dimensions L × W × H (mm)	Weight
160001	FLA-150002	150	150 × 44 × 42	1.6kg
160002	FLA-200002	200	200 × 46 × 42	2.3kg
160003	FLA-250002	250	250 × 46 × 42	2.5kg
160004	FLA-300002	300	300 × 46 × 42	3.2kg

PRECISION LEVEL



- USE**
- Bubble tube indicates horizontal and measures small inclinations
 - For machine installation and general mechanical assembly

FEATURES

- Quality cast iron(FC250) with perfect seasoning and lapped to a fine finish to maintain precision
- Sensitivity : 0.02mm/m

Order No.	Model No.	Standard (mm)	Dimensions L × W × H (mm)	Weight
160005	FLW-150002	150	150 × 44 × 42	1.6kg
160006	FLW-200002	200	200 × 46 × 42	2.3kg
160007	FLW-250002	250	250 × 46 × 42	2.5kg
160008	FLW-300002	300	300 × 46 × 42	3.2kg