

LEVEL MATE



Analog inclinometer with magnet on right vertical surface



USE

- Tilt angle measurement

MATERIAL



- Plastic

FEATURES

- Setting angles for machine work
- Mechanical assembly, installation
- Miscellaneous plumbing work
- Construction and related work
- V grooved on bottom, magnet on vertical surface

SPECIFICATIONS

- Measuring range: 0~360°
- Minimum reading: 1°
- Accuracy: ±0.5°



Order No.	Model No.	Dimensions H × W × T (mm)	Weight
011030	LM-360	110 × 110 × 20	140g

LEVELNIC

PRECISION LEVEL

ANGLE

LEVEL

PROTRACTOR



DIAL SLANT RULE KAIDAN



Analog angle meter with new stepped millimeter graduations that prevents misreading



DSR-180KD



DSRM-180KD
(with magnet)

USE

- Inclination angle measurement

MATERIAL

- Body: ABS ● Cover: Styrol

FEATURES

- Easier to read compared to bubble level
- Kaidan style graduation for easy reading
- Lightweight and handy ● With handle and hook hole

SPECIFICATIONS

- Measuring range: 0~180° ● Graduation: 1°
- Accuracy: ±0.5°



Dual scales for Angle & Inclination measurement

Order No.	Model No.	Type	Magnetic Attraction (Reference Value)	Dimensions L × H × W (mm)	Weight
011002	DSR-180KD	-	-	182 × 92 × 20	110g
011003	DSRM-180KD	with magnet	8N	182 × 92 × 20	112g