

BEVEL BOX BB-180L



Compact design digital inclinometer

Large LCD with backlight for easy reading in a dark place



USE

- For all processes that requires precise angle measurement, such as assembly, molding, machining and fixtures

MATERIAL

- Body: Aluminum (with magnet on base)


FEATURES

- Zero setting at desired position
- Large LCD with backlight for easy reading in a dark place
- "Hold" button to fix reading on display
- Auto power off function (after approx. 5 min.)

POWER

- One AAA battery (NOT included in the package)

● DIMENSIONS Units: mm



※ Quantization Error (± 1 digit) not included


Order No.	Model No.	Measuring Range	Resolution	Operating Temperature	Accuracy [®]	Repeatability	Weight
010103	BB-180L	± 180.0°	0.1°	5 ~ 45°	± 0.2°	0.1°	70g



LEVEL METER KAIDAN



New stepped millimeter graduations prevents misreading.
Analog inclinometer with magnetic base.



USE

- Measurement of inclination angle

MATERIAL

- Body: AS resin ● Cover: Acrylic resin

FEATURES

- Analog dial easier to read than bubble tube type meter
- Stepped length of linear graduations by 1mm for easy-to-read
- Lightweight and handy
- With magnetic base

SPECIFICATIONS

- Measurement range: 0~90°
- Graduation: 1°
- Accuracy: ±0.5°



Order No.	Model No.	Product Type	Magnetic Attraction (Reference Value)	Dimensions H × W × T (mm)	Weight
011012	LM-90KDS	Strong magnet type	40N	95 × 95 × 30	100g
011013	LM-90KD	Regular magnet type	10N	95 × 95 × 30	120g



LEVELNIC
PRECISION LEVEL
ANGLE
LEVEL
PROTRACTOR