


VERNIER CALIPER WITH FINE ADJUSTMENT




Suitable for measuring products of similar size in large quantity



GHB-20

Reference standard for calibration ▶ Block Gauge P42 ~49	For measurement of concave area ▶ Caliper Attachment P163
For holding calipers ▶ Combination Stand P226	Rust prevention ▶ Zerust Film for Steel P380

● DIMENSIONS



Units: mm

Model No.	A	B	C	D	E	F	G
GHB-15	240	82	21	40	83	31.5	17
GHB-20	290	92		50			
GHB-30	390	102		60			

USE

- For outside diameter, inside diameter, step and depth measurement

MATERIAL

- Stainless steel

FEATURES


- Mono block vernier caliper
- Integrated vernier type for easy reading
- Provided with a fine adjustment carriage to feed the slider finely
- Satin finish

Order No.	Model No.	Measuring Range (mm)	Resolution (mm)	Accuracy (mm)	Depth Bar (Yes/None)	Weight
151298	GHB-15	130	0.02	± 0.05	Yes	235g
151299	GHB-20	180				275g
151300	GHB-30	280		± 0.08		330g

VERNIER CALIPER WITH THUMB CLAMP




The slider moves only when the thumb clamp is pressed



GHS-15

Reference standard for calibration ▶ Block Gauge P42 ~49	For measurement of concave area ▶ Caliper Attachment P163
For holding calipers ▶ Combination Stand P226	Rust prevention ▶ Zerust Film for Steel P380

● DIMENSIONS



Units: mm

Model No.	A	B	C	D	E	F	G
GHS-15	236	77	16.5	40	56.5	31	16
GHS-20	286	90	19.5	50			

USE

- For outside diameter, inside diameter, step and depth measurement

MATERIAL

- Stainless steel

FEATURES

- Mono block vernier caliper
- Integrated vernier type for easy reading
- Thumb clamp type
- Satin finish

Order No.	Model No.	Measuring Range (mm)	Resolution (mm)	Accuracy (mm)	Depth Bar (Yes/None)	Weight
151367	GHS-15	150	0.05	± 0.05	Yes	160g
151368	GHS-20	200				200g