

INTERCHANGEABLE ROD TYPE DEPTH MICROMETER




For high precision measurement of depth.
Wide measuring range by interchangeable rods.

Reference standard for calibration Block Gauge P42 ~49	Rust prevention Zerust Film for Steel P380
--	--



DIMENSIONS



Units: mm

Model No.	A	B	C	D	E
MC202-50F	63	9	4.5	18	17
MC202-50FS	101.5				
MC202-100F	63				
MC202-100FS	101.5				

USE

- For depth measurement

MATERIAL

- Base: Stainless
- Probe: High carbon chrome steel

FEATURES

- Able to provide a wide measuring range
- With ratchet stop
- Interchangeable rod MC202-50F, MC202-50FS: 2 pcs (25,50mm)
MC202-100F, MC202-100FS: 4 pcs (25,50,75,100mm)

Order No.	Model No.	Measuring Range (mm)	Resolution (mm)	Maximum Error (μm)	Weight
152211	MC202-50F	0 ~ 50	0.01	4	185g
152212	MC202-50FS				265g
152213	MC202-100F	0 ~ 100		5	185g
152214	MC202-100FS				265g

SETTING STANDARD

For origin setting of outside micrometers



Rust prevention Zerust Film for Steel P380
--

Units: mm

DIMENSIONS



Model No.	L
A010-25	25
A020-50	50
A030-75	75
A040-100	100
A050-125	125
A060-150	150
A070-175	175
A080-200	200

USE

- For accurate origin setting of outside micrometers (for size 25~50 and larger size) at the start or end of the measuring range

MATERIAL

- Body: High Carbon chrome steel ● Grip: Plastic

Order No.	Model No.	Micrometer size	Accuracy (μm)	Dimension (mm)	Weight
151491	A010-25	25 ~ 50	± 2	φ 7	10g
151492	A020-50	50 ~ 75			15g
151493	A030-75	75 ~ 100	± 2.5		25g
151494	A040-100	100 ~ 125	± 3	φ 8	45g
151495	A050-125	125 ~ 150	± 3.5		50g
151496	A060-150	150 ~ 175	± 4		65g
151497	A070-175	175 ~ 200	± 4.5		75g
151498	A080-200	200 ~ 225	± 5		85g



MICRO METER

MICRO METER STAND