

PENCIL-TYPE RECIPROCATING POLISHING FINISHER

SWING-LUSTER Attachment


Stroke Range 0~1.6 mm

Right to Left Motion

Exclusive Tools p.5-23~24



- High speed grinding and polishing operations can be performed while maintaining the fine and delicate feel of hand polishing.
- Lightweight pencil type design makes it easy to work in tight areas.
- Ergonomically designed to provide high sensitivity for precision work.
- Easily adjustable stroke length allows efficient work on minute areas of large sections.



The stroke range is bigger in proportion to the distance from the fulcrum.

30,000 min⁻¹ Max.

- ◆ Reciprocating Stroke (variable) : 0~7,650 times/min
- ◆ Stroke Range (variable) : 0~1.6 mm
- ◆ Weight : 127 g
- ◆ Max. tool shank diameter ø5.0 mm, Screw clamp type

Exclusive Tools p.5-23~24



Code No.	1380	Model	SLS-16
----------	-------------	-------	---------------

Standard Accessories

- Wrench (16 x 18), (20 x 24) : 1 pc. each
- Allen Wrench (1.5 mm) : 1 pc.
- Standard Accessories : 1 set


SWING-LUSTER Attachment + Standard Type Motor Combination Example
Reciprocating Stroke
0~7,650 times/min

Emax EVOLution Controller (p.1-7)

<Code No. : 8224 (120V) · Model : NE249 120>

<Code No. : 8227 (230V) · Model : NE249 230>

Never connect to E-max Series Controller.



Combination Example	Outside Diameter	Weight	Max. Torque	Reciprocating Stroke	Max. Tool Shank
1380+8086	Refer to the dimensions	217 g (*)	4.3 cN·m	0~7,650 times/min	ø5.0 mm (screw clamp type)

Standard Accessories

Code No.	Description	Package
62510	Ceramic Fiber Grindstone Holder	1 pc. each
62814	Electroplated Diamond File 1.25 x 4 x 50 #100	
60520	Ceramic Fiber Grindstone 1 x 6 x 50 #1200	

• Exclusive tools p.5-23~24

※ Weight (w/o Straight Cord)