












■ Collet · Collet Nut

Product	Code No.	Model	I.D.	Compatible model	
 <p>Collet CHA Group</p>	<b>91494</b>	CHA-3.0AA	ø3.0AA ※	MSS-19, MSS-20, MSS-22 PMS-3020A ※ High precision type AA (Run-out Accuracy within 2 μm)	
	<b>91496</b>	CHA-3.175AA	ø3.175AA ※		
	<b>91495</b>	CHA-4.0AA	ø4.0AA ※		
	<b>91492</b>	CHA-2.35	ø2.35		
	<b>91430</b>	CHA-3.0	ø3.0		
	<b>91493</b>	CHA-3.175	ø3.175		
	<b>91440</b>	CHA-4.0	ø4.0		
 <p>Collet CHA Group</p>	—	CHA-□□	ø0.5, ø0.6, ø0.7, ø0.8, ø0.9 ø1.1, ø1.2, ø1.3, ø1.4, ø1.7, ø1.8, ø1.9 ø2.1, ø2.2, ø2.3, ø2.4, ø2.6, ø2.7, ø2.8, ø2.9 ø3.1, ø3.2, ø3.3, ø3.4, ø3.6, ø3.7, ø3.8, ø3.9 ø1.0, ø1.5, ø2.0, ø2.5, ø3.5 ø1.6		
	 <p>Collet CHK Group</p>	<b>91597</b>	CHK-3.0AA	ø3.0AA ※	MSS-25, MSST-23, NR-2351, NR-2551 NR-303, NR-311, NR-3060S, NR-3060 NR-403E, NR-453E, PMA-3013K PMS-3020K, PMR-3005K, RAS-101 RAS-151E, RAX-71E, RAX-271E ※ High precision type AA (Run-out Accuracy within 2 μm)
		<b>91598</b>	CHK-3.175AA	ø3.175AA ※	
		<b>91599</b>	CHK-4.0AA	ø4.0AA ※	
<b>91600</b>		CHK-6.0AA	ø6.0AA ※		
<b>91601</b>		CHK-6.35AA	ø6.35AA ※		
<b>91592</b>		CHK-2.35	ø2.35		
<b>91530</b>		CHK-3.0	ø3.0		
<b>91593</b>		CHK-3.175	ø3.175		
<b>91540</b>		CHK-4.0	ø4.0		
<b>91560</b>		CHK-6.0	ø6.0		
 <p>Collet CHK Group</p>	—	CHK-□□	ø0.5, ø0.6, ø0.7, ø0.8, ø0.9 ø1.0, ø1.5, ø2.0, ø2.5, ø3.5, ø4.5, ø4.76, ø5.5 ø1.1, ø1.2, ø1.3, ø1.4, ø1.7, ø1.8, ø1.9 ø2.1, ø2.2, ø2.3, ø2.4, ø2.6, ø2.7, ø2.8, ø2.9 ø3.1, ø3.2, ø3.3, ø3.4, ø3.6, ø3.7, ø3.8, ø3.9 ø4.1, ø4.2, ø4.3, ø4.4, ø4.6, ø4.7, ø4.8, ø4.9 ø5.1, ø5.2, ø5.3, ø5.4, ø5.6, ø5.7, ø5.8, ø5.9 ø1.6, ø5.0		
	 <p>Collet CHSS Group</p>	<b>93092</b>	CHSS-2.35	ø2.35	PMA-3013S
		<b>93030</b>	CHSS-3.0	ø3.0	
		<b>93093</b>	CHSS-3.175	ø3.175	
—		CHSS-□□	ø1.0, ø1.5, ø2.0, ø2.5		
 <p>Collet CHM Group</p>	<b>90992</b>	CHM-2.35	ø2.35	AMH-301, NR-601	
	<b>90930</b>	CHM-3.0	ø3.0		
	<b>90993</b>	CHM-3.175	ø3.175		
	<b>90916</b>	CHM-1.6	ø1.6		
 <p>Collet CHM Group</p>	—	CHM-□□	ø1.0, ø2.0		
	 <p>Collet CHS Group</p>	<b>90592</b>	CHS-2.35	ø2.35	RA-200, RA-271E
<b>90530</b>		CHS-3.0	ø3.0		
<b>90593</b>		CHS-3.175	ø3.175		
<b>90516</b>		CHS-1.6	ø1.6		
—		CHS-□□	ø0.8, ø0.9 ø1.0, ø2.0, ø2.5 ø1.1, ø1.2, ø1.3, ø1.4, ø1.5, ø1.7, ø1.8, ø1.9 ø2.1, ø2.2, ø2.3, ø2.4, ø2.6, ø2.7, ø2.8, ø2.9		
 <p>Collet CH8 Group</p>	<b>91092</b>	CH8-2.35	ø2.35	RA-100, RA-151E	
	<b>91030</b>	CH8-3.0	ø3.0		
	<b>91093</b>	CH8-3.175	ø3.175		
	—	CH8-□□	ø0.8, ø0.9 ø1.0, ø1.5, ø2.0, ø2.5 ø1.1, ø1.2, ø1.3, ø1.4, ø1.6, ø1.7, ø1.8, ø1.9 ø2.1, ø2.2, ø2.3, ø2.4, ø2.6, ø2.7, ø2.8, ø2.9		
	<b>2102</b>	CHN-A	Collet Nut for Collet (CHA)	MSS-19, MSS-20, MSS-22 PMS-3020A	
	<b>2129</b>	K-265	Collet Nut for Collet (CHK)	MSS-25, MSST-23, NR-2351, NR-2551, NR-303 NR-311, NR-3060S, NR-3060, NR-403E NR-453E, PMA-3013K, PMS-3020K, PMR-3005K RAS-101, RAS-151E, RAX-71E, RAX-271E	