


PRESTO II AIR TURBINE GRINDER ◀◀

ULTRA-HIGH SPEED AIR TURBINE GRINDER



# PRESTO II

320,000 min<sup>-1</sup>

ø1.6 mm Bur Only

- An astonishing 320,000 rpm. Smooth cutting without any resistance enables precise cutting and processing.
- Clean cutting is possible with the oilless air grinder. No oil sprays out to prevent the workpieces and hands from getting dirty.
- Lightweight aluminum body (71 g) with a palm-sized overall length (109 mm). High-precision processing of minute parts is possible at the same touch when holding a ball-point pen.

PRESTO II Standard Set

Code No. **1125**

Model **PRII-304S**

Standard Equipment

- Presto Handpiece (PR-304) : 1 pc.
- Air Line Kit (PRII-06) : 1 pc.
- Foot Controller (AFC-40) : 1 pc.
- Handpiece Holder (Z014) : 1 pc.



Specifications

Rotating Speed	: 320,000 min <sup>-1</sup>
Proper Air Pressure	: 0.25 MPa
Air Consumption	: 40 Nℓ/min
Inside Diameter	: ø1.6 mm Bur Only
Filter Mesh	: 5 μm

PRESTO Handpiece

**320,000 min<sup>-1</sup>**

Code No. **1122**

Model **PR-304**

◆ Weight : 71 g (w/o Hose)

Standard Accessories

- 2 m Hose



- Ultra-high speed no lube air turbine handpiece ideal for delicate processing application.
- Built-in dust protection mechanism developed by NAKANISHI ensures long durability.
- Chip air blows away the cutting powder and cools the cutting tool.
- Flexible tubing ensures excellent workability reducing fatigue to the operator's hand for long continuous use.

PRESTO II Spare Parts

Product	Description / Specifications	Code No.	Model
	PRESTO II Air Line Kit (w/o Lubricator / Filter Mesh 5 μm)	<b>1126</b>	PRII-06
	PRESTO II Cartridge	<b>1120</b>	PR-03
	Foot Controller	<b>1124</b>	AFC-40
	Piping Hose (ø6.0) 2 m Long	<b>2041</b>	K-237
	Air Turbine Hose (ø5.1) 2 m Long	<b>2042</b>	K-238
	Pin Wrench	<b>2002</b>	T-751

ø1.6 mm tools for PRESTO II



CAUTION

Electric System

Air System

Ultrasonic

General Parts

Exclusive Tools