




溝付きピン E形 DIN 1475

材質 快削鋼

表面処理 呼び径4以上は黒染

仕様・規格・サイズ表



呼び寸法 d X L

d	C	L								
		D								
1.5	h9	0.2	8	10	12	16	20			
			1.6	1.6	1.6	1.63	1.63			
2	h9	0.25	12	16	20					
			2.1	2.1	2.1					
2.5	h9	0.3	12	16	20	26				
			2.6	2.6	2.65	2.65				
3	h9	0.4	12	16	20	26	30			
			3.1	3.1	3.15	3.2	3.2			
4	h11	0.5	20	26	30	36	40	45		
			4.15	4.2	4.2	4.25	4.25	4.25		
5	h11	0.6	20	26	30	36	40	45		
			5.15	5.2	5.2	5.25	5.25	5.25		
6	h11	0.8	26	30	36	40	45	50	55	60
			6.25	6.25	6.25	6.3	6.3	6.3	6.3	6.3
8	h11	1.0	26	30	36	40	45	50	55	60
			8.2	8.2	8.25	8.3	8.3	8.35	8.35	8.35