



3-flute CBN corner radius end mill.
Realized high efficient and high accurate machining



- Realized high accuracy and high efficiency machining by adopting 3 flutes and corner R with spiral shape.



Cutting edge shape

Unit : mm

Code No.	Dia. (D)	Corner Radius (R)	Under Neck Length (ℓ1)	Length of Cut (ℓ)	Neck Dia. (d2)	Neck Taper Angle (γ)	Shank Dia. (d)	Overall Length (L)
01-00495-05011	0.5	R0.1	1.5	0.25	0.46	15°	4	50
01-00495-05012			2.5	0.25	0.46	15°	4	50
01-00495-10011	1	R0.1	3	0.5	0.95	15°	4	50
01-00495-10012			5	0.5	0.95	15°	4	52
01-00495-10021		R0.2	3	0.5	0.95	15°	4	50
01-00495-10022			5	0.5	0.95	15°	4	52
01-00495-15011	1.5	R0.1	4.5	0.75	1.45	15°	4	52
01-00495-15012			7.5	0.75	1.45	15°	4	52
01-00495-15021		R0.2	4.5	0.75	1.45	15°	4	52
01-00495-15022			7.5	0.75	1.45	15°	4	52
01-00495-20011	2	R0.1	6	1	1.94	15°	4	52
01-00495-20012			10	1	1.94	15°	4	52
01-00495-20031		R0.3	6	1	1.94	15°	4	52
01-00495-20032			10	1	1.94	15°	4	52

How to Order

When you order, indicate SHR320 (D)×(R)×(ℓ1). ※(γ) is reference value.

