

Reamers

Endmills

Drills

Countersinks/
Counterbores

Slitting Saws/
Cut-off tools

Cutters

Side
Milling

Staggered


Angle

Plain

for Pipe

SC

サイドカッター
Side Milling Cutters



厚み(T)の寸法許容差
Tolerance of thickness(T)

厚み(T) Thickness(T)	許容差 Tolerance
3.0以下 3.0 or less	+0.060 0
3.0をこえ6.0以下 6.0 or less exceeding 3.0	+0.075 0
6.0をこえ10.0以下 10.0 or less exceeding 6.0	+0.090 0
10.0をこえ18.0以下 18.0 or less exceeding 10.0	+0.110 0
18.0をこえ30.0以下 30.0 or less exceeding 18.0	+0.130 0
30.0をこえ50.0以下 50.0 or less exceeding 30.0	+0.160 0



- 外径、厚みが豊富
Wide variety of diameters and thicknesses
- 溝削り、段削り、側面削り加工
Slitting, step cutting, side milling
- MCO材(コバルト高速度鋼)を使用
Uses MCO material (Cobalt high-speed steel)

穴径φ25.4 Hole Dia.φ25.4

品番 Product No.	寸法 Size				標準価格 Standard price ¥
	刃径 D	厚み T	穴径 d	刃数 NT	
SCT060X030	60	3	25.4	22	9,500
SCT060X040	60	4	25.4	22	9,500
SCT060X050	60	5	25.4	22	9,200
SCT060X060	60	6	25.4	20	9,200
SCT060X070	60	7	25.4	20	10,000
SCT060X080	60	8	25.4	20	10,600
SCT060X090	60	9	25.4	20	11,100
SCT060X100	60	10	25.4	20	11,800
SCT060X110	60	11	25.4	20	12,400
SCT060X120	60	12	25.4	20	12,800
SCT060X130	60	13	25.4	20	13,500
SCT060X140	60	14	25.4	20	13,700
SCT060X150	60	15	25.4	20	14,300
SCT060X160	60	16	25.4	20	15,000
SCT060X170	60	17	25.4	20	17,000
SCT060X180	60	18	25.4	20	17,000
SCT060X190	60	19	25.4	20	17,400
SCT060X200	60	20	25.4	20	19,000
SCT060X210	60	21	25.4	20	19,200
SCT060X220	60	22	25.4	20	20,900
SCT065X030	65	3	25.4	22	10,500
SCT065X040	65	4	25.4	22	10,500
SCT065X050	65	5	25.4	22	10,500
SCT065X060	65	6	25.4	20	10,500
SCT065X070	65	7	25.4	20	11,000
SCT065X080	65	8	25.4	20	11,800
SCT065X090	65	9	25.4	20	12,500
SCT065X100	65	10	25.4	20	13,100
SCT065X110	65	11	25.4	20	13,600
SCT065X120	65	12	25.4	20	14,200
SCT065X130	65	13	25.4	20	14,900
SCT065X140	65	14	25.4	20	15,500

※φ60・65・80・90は生産終了につき在庫限りとなります。

品番 Product No.	寸法 Size				標準価格 Standard price ¥
	刃径 D	厚み T	穴径 d	刃数 NT	
SCT065X150	65	15	25.4	20	16,200
SCT065X160	65	16	25.4	20	17,000
SCT065X170	65	17	25.4	20	18,200
SCT065X180	65	18	25.4	20	19,200
SCT065X190	65	19	25.4	20	20,000
SCT065X200	65	20	25.4	20	21,600
SCT075X030	75	3	25.4	24	11,500
SCT075X035	75	3.5	25.4	24	11,500
SCT075X040	75	4	25.4	24	11,500
SCT075X045	75	4.5	25.4	24	10,500
SCT075X050	75	5	25.4	24	10,500
SCT075X055	75	5.5	25.4	24	10,100
SCT075X060	75	6	25.4	24	10,100
SCT075X065	75	6.5	25.4	24	11,200
SCT075X070	75	7	25.4	24	11,200
SCT075X075	75	7.5	25.4	24	11,200
SCT075X080	75	8	25.4	22	11,200
SCT075X085	75	8.5	25.4	22	12,300
SCT075X090	75	9	25.4	22	12,300
SCT075X095	75	9.5	25.4	22	12,300
SCT075X100	75	10	25.4	22	12,300
SCT075X105	75	10.5	25.4	22	13,100
SCT075X110	75	11	25.4	22	13,100
SCT075X120	75	12	25.4	22	13,100
SCT075X130	75	13	25.4	22	14,700
SCT075X140	75	14	25.4	22	14,700
SCT075X150	75	15	25.4	22	16,000
SCT075X160	75	16	25.4	22	16,000
SCT075X170	75	17	25.4	22	18,400
SCT075X180	75	18	25.4	22	18,400
SCT075X190	75	19	25.4	22	22,600
SCT075X200	75	20	25.4	22	22,600