




Short Hinge Lever
X-10GW21-B




Hinge Lever
X-10GW-B




Low-force Hinge Lever
X-10GW4-B




Short Hinge Roller Lever
X-10GW22-B




Hinge Roller Lever
X-10GW2-B




Reverse Hinge Lever
X-10GM-B



Reverse Short Hinge Lever
X-10GM22-B



Reverse Hinge Roller Lever
X-10GM2-B



Note: Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

Model		X-10GW21-B	X-10GW-B	X-10GW4-B	X-10GW22-B	X-10GW2-B	X-10GM-B	X-10GM22-B	X-10GM2-B
Operating Characteristics	OF	max.	2.45 N	1.08 N	0.25 N	2.16 N	1.42 N	2.16 N	3.14 N
	RF	min.	0.31 N	0.14 N	0.05 N	0.34 N	0.21 N	0.25 N	0.49 N
	PT	max.	—	—	14.3 mm	—	—	—	—
	OT	min.	2.1 mm	4.8 mm	4.8 mm	2.4 mm	4 mm	5.5 mm	4 mm
	MD	max.	1.7 mm	3.9 mm	3.9 mm	1.7 mm	3 mm	2.1 mm	1.5 mm
FP	max.	25.5 mm	34.6 mm	—	37.1 mm	40.5 mm	26.8 mm	36.1 mm	37.4 mm
		20.7 \pm 0.8 mm	21.1 \pm 0.8 mm	21.1 \pm 0.8 mm	32.2 \pm 0.8 mm	32.2 \pm 0.8 mm	21.1 \pm 0.8 mm	32.2 \pm 0.8 mm	32.2 \pm 0.8 mm
OP									