


G-LIST No | FW1006

インデキサブルドリル 3D用

Indexable Drill for 3D

PHP インサート 切削条件 Cutting Conditions P1067



■適用インサート Inserts

(単位:mm) (Unit:mm)

呼び Designation	切れ刃数 Number of Cutting Edges	適用ボディ Applicable Body	インサート寸法 Insert Size				コーティング材種 Grade of Coated Materials		標準価格 (Yen)
			IC	厚さ S	逃げ角 AN	RE	XP9040	XC9025	
① SCMT042204-DM	4	φ14~16	4.8	2.2	7°	0.4	7818001	7817001	1,610
② SCMT052404-DM	4	φ16.5~18	5.4	2.4	7°	0.4	7818002	7817002	1,610
③ SCMT062806-DM	4	φ18.5~20.5	6.2	2.8	7°	0.6	7818003	7817003	1,660
④ SCMT073206-DM	4	φ21~24	7.2	3.2	7°	0.6	7818004	7817004	1,720
⑤ SCMT083608-DM	4	φ24.5~28	8.6	3.6	7°	0.8	7818005	7817005	1,760
⑥ SCMT104208-DM	4	φ29~34	10	4.2	7°	0.8	7818006	7817006	1,810
⑦ SCMT125008-DM	4	φ35~40	12.3	5	7°	0.8	7818007	7817007	1,870

■部品 Accessories

	ツールNo. EDP No.	呼び Designation	適用インサート Applicable Inserts	
 クランプねじ Clamping Screw	7808100	FS18538 (Torx 6)	①	SCMT042204-DM
	7808102	FS20540 (Torx 6)	②	SCMT052404-DM
	7808104	FS22550 (Torx 7)	③	SCMT062806-DM
	7808108	FS25560 (Torx 8)	④	SCMT073206-DM
	7808110	FS30573 (Torx 8)	⑤	SCMT083608-DM
	7808111	FS35572 (Torx 15)	⑥	SCMT104208-DM
	7808113	FS45510 (Torx 20)	⑦	SCMT125008-DM

	ツールNo. EDP No.	呼び Designation	適用インサート Applicable Inserts		標準価格 (Yen)		
 レンチ Wrench	7808203	T6-D (Torx 6)	①	SCMT042204-DM	②	SCMT052404-DM	1,050
	7808204	T7-D (Torx 7)	③	SCMT062806-DM	—	—	1,050
	7808205	T8-D (Torx 8)	④	SCMT073206-DM	⑤	SCMT083608-DM	1,190
	7808208	T15-D (Torx 15)	⑥	SCMT104208-DM	—	—	1,260
	7808209	T20-D (Torx 20)	⑦	SCMT125008-DM	—	—	1,260

レンチは別途ご購入下さい。 The wrenches are sold separately from the cutters.