

## 工具選定表 Selection Chart

前ページより

FROM 呼び Size M13 ~ M20

ピッチ Pitch	呼び Thread Size	マルチポイント Multi Point		シングルポイント Single Point	
		適応ボディ Tool Body	適応インサート Insert	適応ボディ Tool Body	適応インサート Insert
P1.5	M 22 ~	TM2C20-2	2I 1.5 ISO TM2		
		TMC16-3	3I 1.5 ISO TM2		
	M 24 ~	TMNC20-3	3I 1.5 ISO TM2		
	M 25 ~	TMC20-3	3I 1.5 ISO TM2		
	M 26 ~			TM2SC 18C23-86-2U	2UIDB60 TM
	M 27 ~	TMLC25-3	3I 1.5 ISO TM2		
	M 28 ~			TM3SC 20C26-105-2U	2UIDB60 TM
	M 30 ~	TMC25-5 124/004	5I 1.5 ISO TM2		
	M 31 ~	TM2C25-3	3I 1.5 ISO TM2		
	M 33 ~			TM4SC 25C31-115-2U	2UIDB60 TM
	M 35 ~	TMC25-5, TMLC25-5	5I 1.5 ISO TM2		
	M 39 ~			TM3SC 28C36-144-3U	3UIDB60 TM
	M 40 ~	TMC32-6B	6BI 1.5 ISO TM2		
	M 43 ~	TMC32-5, TMLC32-5, <b>TMNC32-5</b>	5I 1.5 ISO TM2		
	M 45 ~			<b>TM4SC D42-16-3U</b>	3UIDB60 TM
	M 48 ~	TM2C32-5	5I 1.5 ISO TM2		
	M 51 ~	<b>TM40-6B</b>	6BI 1.5 ISO TM2		
	M 52 ~			<b>TM5SC D48-22-3U</b>	3UIDB60 TM
	M 56 ~	TMSH-D50-FMA25.4-3	5I 1.5 ISO TM2		
	M 59 ~	TMLC42-6B	6BI 1.5 ISO TM2		
M 60 ~			TM6SC D56-22-3U	3UIDB60 TM	
M 69 ~	TMSH-D63-FMA25.4-5	5I 1.5 ISO TM2			
M 86 ~	TMSH-D80-FMA25.4-6B	6BI 1.5 ISO TM2			
	TMSH-D80-FMA25.4-5	5I 1.5 ISO TM2			
M106 ~	TMSH-D100-FMA31.75-5	5I 1.5 ISO TM2			
M131 ~	TMSH-D125-FMA38.1-5	5I 1.5 ISO TM2			
P1.75	M 21 ~	TMC16-3 124/001, TMNC16-3	3I 1.75 ISO TM2		
	M 23 ~	TMC16-3	3I 1.75 ISO TM2		
	M 25 ~	TMNC20-3	3I 1.75 ISO TM2		
	M 26 ~	TMC20-3	3I 1.75 ISO TM2		
	M 28 ~	TMLC25-3	3I 1.75 ISO TM2		
	M 31 ~	TMC25-5 124/004	5I 1.75 ISO TM2		
	M 32 ~	TM2C25-3	3I 1.75 ISO TM2		
	M 36 ~	TMC25-5, TMLC25-5	5I 1.75 ISO TM2		
	M 44 ~	TMC32-5, TMLC32-5, <b>TMNC32-5</b>	5I 1.75 ISO TM2		
	M 49 ~	TM2C32-5	5I 1.75 ISO TM2		
	M 57 ~	TMSH-D50-FMA25.4-3	3I 1.75 ISO TM2		
	M 70 ~	TMSH-D63-FMA25.4-5	5I 1.75 ISO TM2		
	M 87 ~	TMSH-D80-FMA25.4-5	5I 1.75 ISO TM2		
M107 ~	TMSH-D100-FMA31.75-5	5I 1.75 ISO TM2			
M132 ~	TMSH-D125-FMA38.1-5	5I 1.75 ISO TM2			
P2	M 14 ~ M21	TMC12-2, TMC20-2	2I 2.0 ISO TM 028/004		
	M 22 ~	TMC16-3 124/001, TMNC16-3	3I 2.0 ISO TM2		
	M 23 ~	TMC16-3	3I 2.0 ISO TM2		
	M 25 ~	TMNC20-3	3I 2.0 ISO TM2		
	M 26 ~	TMC20-3	3I 2.0 ISO TM2	TM2SC 18C23-86-2U	2UIDB60 TM
	M 28 ~	TMLC25-3	3I 2.0 ISO TM2		
	M 29 ~			TM3SC 20C26-105-2U	2UIDB60 TM
	M 32 ~	TMC25-5 124/004	5I 2.0 ISO TM2		
	M 33 ~	TM2C25-3	3I 2.0 ISO TM2		
	M 34 ~			TM4SC 25C31-115-2U	2UIDB60 TM
	M 37 ~	TMC25-5, TMLC25-5	5I 2.0 ISO TM2		
	M 39 ~			TM3SC 28C36-144-3U	3UIDB60 TM
	M 42 ~	TMC32-6B	6BI 2.0 ISO TM2		
	M 44 ~	TMC32-5, TMLC32-5, <b>TMNC32-5</b>	5I 2.0 ISO TM2		
	M 45 ~			<b>TM4SC D42-16-3U</b>	3UIDB60 TM
	M 50 ~	TM2C32-5	5I 2.0 ISO TM2		
	M 52 ~			<b>TM5SC D48-22-3U</b>	3UIDB60 TM

※青文字は受注生産となります。

※ Blue characteres are special order items.

次ページへ  
呼び Size M53 ~ M94 NEXT