

# PERSONAL CO/O<sub>2</sub>/H<sub>2</sub>S MONITOR XX-2200 SERIES

O<sub>2</sub> Oxygen

Toxic Gas



### Features

- Uses continuously for 5,000 hours
- 3 types of alarms : loud buzzer, alarm lamp and vibration
- Available with TWA (Time Weighted Average) concentration display



Safety-Pin Adaptor



Leather Case (optional)



Heat Resistant Leather Case (optional)



Simple Inspection Jig (optional)



Helmet Clip (optional)

## Specifications

Model	XOC-2200		
	XC-2200	XO-2200	XOS-2200
Target gas	Carbon Monoxide	Oxygen	Hydrogen Sulfide
Sensor Type	Electrochemical	Galvanic cell	Electrochemical
Detection Range (Reference Indication)	0 to 300 ppm (300 to 2000 ppm)	0 to 25 vol% (25 to 50 vol%)	0 to 30.0 ppm (30.1 to 100 ppm)
Display resolution	1 ppm	0.1 vol%	0.1 ppm
Alarm Set Value	1st	50 ppm	19.5 vol%
	2nd	150 ppm	18.0 vol%
Response Time	30 sec.	20 sec.	30 sec.
Approvals	Ex ib IIB T3 (TIS) CE		
Operating Temperature & Humidity	-10 to +40°C, 30 to 90 %RH		
Power Source	1 x AAA Alkaline battery, Approx. 5,000 hours		
Dimensions	W65 x H64 x D22 mm		
Weight	Approx. 75 g		
Accessories	1 x AAA Alkaline battery, 1 x Safety pin adaptor		
Options	Leather case, Heat resistant leather case, Simple inspection jig, Helmet clip, etc.		