


# CoroMill® 345 face milling cutter

Coromant Capto®

KAPR

45°



## Metric version

						Dimensions								
DC		CZC <sub>MS</sub>	APMX	CNSC		Ordering code	DCON	DCX	LF			RPMX	CICT	MID
40.0	13	C4	6.0	1	3	345-040C4-13L	40.0	54.1	60.0	3.0	0.60	19600	3	345R-1305
		C4	6.0	1	4	345-040C4-13M	40.0	54.1	60.0	3.0	0.60	19600	4	345R-1305
50.0	13	C5	6.0	1	3	345-050C5-13L	50.0	64.1	60.0	3.0	0.90	17500	3	345R-1305
		C6	6.0	1	3	345-050C6-13L	63.0	64.1	60.0	3.0	1.32	17500	3	345R-1305
		C5	6.0	1	4	345-050C5-13M	50.0	64.1	60.0	3.0	0.90	17500	4	345R-1305
		C6	6.0	1	4	345-050C6-13M	63.0	64.1	60.0	3.0	1.29	17500	4	345R-1305
		C5	6.0	1	5	345-050C5-13H	50.0	64.1	60.0	3.0	0.90	17500	5	345R-1305
		C6	6.0	1	5	345-050C6-13H	63.0	64.1	60.0	3.0	1.30	17500	5	345R-1305
63.0	13	C5	6.0	1	4	345-063C5-13L	50.0	78.1	60.0	3.0	1.05	15500	4	345R-1305
		C6	6.0	1	4	345-063C6-13L	63.0	77.1	60.0	3.0	1.50	15500	4	345R-1305
		C5	6.0	1	5	345-063C5-13M	50.0	77.1	60.0	3.0	1.05	15500	5	345R-1305
		C6	6.0	1	5	345-063C6-13M	63.0	77.1	60.0	3.0	1.50	15500	5	345R-1305
		C5	6.0	1	6	345-063C5-13H	50.0	78.1	60.0	3.0	1.07	15500	6	345R-1305
		C6	6.0	1	6	345-063C6-13H	63.0	77.1	60.0	3.0	1.50	15500	6	345R-1305
80.0	13	C6	6.0	1	4	345-080C6-13L	63.0	94.1	70.0	3.0	2.00	13700	4	345R-1305
		C6	6.0	1	6	345-080C6-13M	63.0	94.1	70.0	3.0	2.04	13700	6	345R-1305
		C8	6.0	1	6	345-080C8-13M	80.0	94.1	70.0	3.0	2.80	13700	6	345R-1305
		C6	6.0	1	8	345-080C6-13H	63.0	94.1	70.0	3.0	2.00	13700	8	345R-1305
		C8	6.0	1	8	345-080C8-13H	80.0	94.1	70.0	3.0	2.80	13700	8	345R-1305
100.0	13	C8	6.0	1	7	345-100C8-13M	80.0	114.1	80.0	3.0	3.68	12200	7	345R-1305
		C8	6.0	1	10	345-100C8-13H	80.0	114.1	80.0	3.0	3.73	12200	10	345R-1305

