



# CoroMill® 419 insert for milling


KRINS 419N..E-SM / 419N..M-KH  
19°



419R..E-MM / 419R..M-PH / 419R..M-PM  
19°



	RE	BS	Ordering code	Dimensions, mm, inch																							
				P			M			K			S			H											
				1030	4230	4240	1030	1040	2040	530T	840T	1020	3040	3330	4230	1030	1040	2040	530T	840T	1010	1030	IC	LE	S		
Medium	14	0.8	2.0	419R-1405M-PM	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	☆	13.5	9.0	5.47	
		.031	.079																					.531	.354	.215	
	14	0.8	2.0	419R-1405E-MM	☆	☆		☆	☆	☆	☆					☆	☆	☆	☆	☆	☆	☆	☆	13.5	9.0	5.47	
		.031	.079																					.531	.354	.215	
Heavy	14	3.0		419N-140530E-SM	☆	☆	☆	☆	☆	☆	☆	☆				☆	☆	☆	☆	☆	☆	☆	☆	13.5	9.0	5.47	
		.118																						.531	.354	.215	
	14	0.8	2.0	419R-1405M-PH		☆	☆	☆						☆	☆	☆						☆		13.5	9.0	5.47	
		.031	.079																					.531	.354	.215	
	14	3.0		419N-140530M-KH		☆	☆						☆	☆	☆	☆								13.5	9.0	5.47	
		.118																						.531	.354	.215	




J474



J508



Q1



Q17

