


# CoroMill® 245 face milling cutter

Arbor

STDNO ISO 6462:2011  
KAPR 45°



## Metric version

							Dimensions									
DC	CZC <sub>MS</sub>	APMX	CNSC		Ordering code	DCON	ISO	DBC	DCX	LF			RPMX	CICT	MID	
50.0	12	22	6.0	0	3	R245-050Q22-12L	22.0	A	62.5	40.0	3.0	0.65	16250	3	R245-12T3..	
	12	22	6.0	0	4	R245-050Q22-12M	22.0	A	62.5	40.0	3.0	0.60	16250	4	R245-12T3..	
	12	22	6.0	0	5	R245-050Q22-12H	22.0	A	62.5	40.0	3.0	0.50	16250	5	R245-12T3..	
63.0	12	22	6.0	0	4	R245-063Q22-12L	22.0	A	75.5	40.0	3.0	0.79	14400	4	R245-12T3..	
	12	22	6.0	0	5	R245-063Q22-12M	22.0	A	75.5	40.0	3.0	0.79	14400	5	R245-12T3..	
	12	22	6.0	0	6	R245-063Q22-12H	22.0	A	75.5	40.0	3.0	0.58	14400	6	R245-12T3..	
80.0	12	27	6.0	0	4	R245-080Q27-12L	27.0	B	92.5	50.0	3.0	1.42	12700	4	R245-12T3..	
	12	27	6.0	0	6	R245-080Q27-12M	27.0	B	92.5	50.0	3.0	1.42	12700	6	R245-12T3..	
	12	27	6.0	0	8	R245-080Q27-12H	27.0	B	92.5	50.0	3.0	0.97	12700	8	R245-12T3..	
	18	32	10.0	0	4	R245-080Q32-18M	32.0	B	98.8	50.0	5.0	1.62	6100	4	R245-18T6..	
	18	32	10.0	0	5	R245-080Q32-18H	32.0	B	98.8	50.0	5.0	1.60	6100	5	R245-18T6..	
100.0	12	32	6.0	0	5	R245-100Q32-12L	32.0	B	112.5	50.0	3.0	1.87	11300	5	R245-12T3..	
	12	32	6.0	0	7	R245-100Q32-12M	32.0	B	112.5	50.0	3.0	1.87	11300	7	R245-12T3..	
	12	32	6.0	0	10	R245-100Q32-12H	32.0	B	112.5	50.0	3.0	1.42	11300	10	R245-12T3..	
	18	32	10.0	0	4	R245-100Q32-18M	32.0	B	118.8	50.0	5.0	1.87	5400	4	R245-18T6..	
	18	32	10.0	0	6	R245-100Q32-18H	32.0	B	118.8	50.0	5.0	1.87	5400	6	R245-18T6..	
	18	32	10.0	0	7	R245-100Q32-18H	32.0	B	118.8	50.0	5.0	1.87	5400	7	R245-18T6..	
125.0	12	40	6.0	0	6	R245-125Q40-12L	40.0	B	137.5	63.0	3.0	3.16	10100	6	R245-12T3..	
	12	40	6.0	0	8	R245-125Q40-12M	40.0	B	137.5	63.0	3.0	3.16	10100	8	R245-12T3..	
	12	40	6.0	0	12	R245-125Q40-12H	40.0	B	137.5	63.0	3.0	2.60	10100	12	R245-12T3..	
	18	40	10.0	0	5	R245-125Q40-18M	40.0	B	138.8	63.0	5.0	3.80	4900	5	R245-18T6..	
	18	40	10.0	0	7	R245-125Q40-18H	40.0	B	138.8	63.0	5.0	3.80	4900	7	R245-18T6..	
	18	40	10.0	0	9	R245-125Q40-18H	40.0	B	138.8	63.0	5.0	3.80	4900	9	R245-18T6..	
160.0	12	40S	6.0	0	7	R245-160Q40-12L	40.0	C	66.7	172.5	63.0	3.0	5.00	8900	7	R245-12T3..
	12	40S	6.0	0	10	R245-160Q40-12M	40.0	C	66.7	172.5	63.0	3.0	5.00	8900	10	R245-12T3..
	12	40S	6.0	0	16	R245-160Q40-12H	40.0	C	66.7	172.5	63.0	3.0	5.00	8900	16	R245-12T3..
	18	40S	10.0	0	6	R245-160Q40-18M	40.0	C	66.7	178.8	63.0	5.0	8.50	4300	6	R245-18T6..
	18	40S	10.0	0	9	R245-160Q40-18H	40.0	C	66.7	178.8	63.0	5.0	8.50	4300	9	R245-18T6..
200.0	12	60	6.0	0	8	R245-200Q60-12L	60.0	C	101.6	212.5	63.0	3.0	6.70	7950	8	R245-12T3..
	12	60	6.0	0	12	R245-200Q60-12M	60.0	C	101.6	212.5	63.0	3.0	6.70	7950	12	R245-12T3..
	12	60	6.0	0	20	R245-200Q60-12H	60.0	C	101.6	212.5	63.0	3.0	6.70	7950	20	R245-12T3..
	18	60	10.0	0	8	R245-200Q60-18M	60.0	C	101.6	218.8	63.0	5.0	12.00	3800	8	R245-18T6..
	18	60	10.0	0	12	R245-200Q60-18H	60.0	C	101.6	218.8	63.0	5.0	12.00	3800	12	R245-18T6..
	18	60	10.0	0	14	R245-200Q60-18H	60.0	C	101.6	218.8	63.0	5.0	12.00	3800	14	R245-18T6..
250.0	12	60	6.0	0	10	R245-250Q60-12L	60.0	C	101.6	262.5	63.0	3.0	8.70	7100	10	R245-12T3..
	12	60	6.0	0	14	R245-250Q60-12M	60.0	C	101.6	262.5	63.0	3.0	8.80	7100	14	R245-12T3..
	12	60	6.0	0	24	R245-250Q60-12H	60.0	C	101.6	262.5	63.0	3.0	8.66	7100	24	R245-12T3..
	18	60	10.0	0	10	R245-250Q60-18M	60.0	C	101.6	268.8	63.0	5.0	8.82	3400	10	R245-18T6..
	18	60	10.0	0	14	R245-250Q60-18H	60.0	C	101.6	268.8	63.0	5.0	8.80	3400	14	R245-18T6..

