


CoroMill® 490 square shoulder milling cutter

Cylindrical shank

KAPR

90°



Metric version

						Dimensions									
DC	CZC _{MS}	APMX	CNSC	Ordering code	DCON	DCX	LF	LU	RPM	kg	RPMX	CICT	MIID		
20.0	08	16	5.5	1	2	490-020A16-08L	16.0	20.0	100.0	1.2	0.18	48500	2	490R-08T308	
	08	20	5.5	1	2	490-020A20-08L	20.0	20.0	110.0	25.0	1.2	0.23	48500	2	490R-08T308
22.0	08	20	5.5	1	2	490-022A20L-08L	20.0	22.0	170.0		1.2	0.40	20300	2	490R-08T308
25.0	08	20	5.5	1	2	490-025A20-08L	20.0	25.0	110.0		1.2	0.23	40400	2	490R-08T308
	08	25	5.5	1	2	490-025A25-08L	25.0	25.0	120.0	32.0	1.2	0.40	40400	2	490R-08T308
08	20	5.5	1	3	490-025A20-08M	20.0	25.0	110.0		1.2	0.23	40400	3	490R-08T308	
	08	25	5.5	1	3	490-025A25-08M	25.0	25.0	120.0	32.0	1.2	0.40	40400	3	490R-08T308
28.0	08	25	5.5	1	2	490-028A25L-08L	25.0	28.0	210.0		1.2	0.80	11000	2	490R-08T308
32.0	08	25	5.5	1	3	490-032A25-08L	25.0	32.0	120.0		1.2	0.44	33900	3	490R-08T308
	08	32	5.5	1	3	490-032A32-08L	32.0	32.0	130.0	40.0	1.2	0.70	33900	3	490R-08T308
08	25	5.5	1	4	490-032A25-08M	25.0	32.0	120.0		1.2	0.44	33900	4	490R-08T308	
	08	32	5.5	1	4	490-032A32-08M	32.0	32.0	130.0	40.0	1.2	0.70	33900	4	490R-08T308
40.0	08	32	5.5	1	3	490-040A32-08L	32.0	40.0	170.0		1.2	1.08	20300	3	490R-08T308
	08	32	5.5	1	4	490-040A32-08M	32.0	40.0	170.0		1.2	1.08	20300	4	490R-08T308
08	32	5.5	1	6	490-040A32-08H	32.0	40.0	170.0		1.2	1.08	20300	6	490R-08T308	
	14	32	10.0	1	3	490-040A32-14M	32.0	40.0	170.0		3.0	1.00	26400	3	490R-1404
14	32	10.0	1	3	490-040A32L-14M	32.0	40.0	250.0		3.0	1.51	7600	3	490R-1404	
	14	32	10.0	1	4	490-040A32-14H	32.0	40.0	170.0		3.0	1.00	26400	4	490R-1404
50.0	14	32	10.0	1	3	490-050A32-14L	32.0	50.0	120.0		3.0	0.82	13700	3	490R-1404
	14	32	10.0	1	4	490-050A32-14M	32.0	50.0	120.0		3.0	0.82	13700	4	490R-1404
63.0	14	32	10.0	1	4	490-063A32-14L	32.0	63.0	120.0		3.0	1.00	11700	4	490R-1404
	14	32	10.0	1	5	490-063A32-14M	32.0	63.0	120.0		3.0	1.00	11700	5	490R-1404

