


CoroMill® 490 square shoulder milling cutter

Weldon

KAPR

90°



Metric version

						Dimensions									
DC		CZC _{MS}	APMX	CNSC		Ordering code	DCON	DCX	LF	LU			RPMX	CICT	MIID
20.0	08	16	5.5	1	2	490-020B16-08L	16.0	20.0	74.0		1.2	0.10	48500	2	490R-08T308
	08	20	5.5	1	2	490-020B20-08L	20.0	20.0	76.0	25.0	1.2	0.18	48500	2	490R-08T308
25.0	08	20	5.5	1	2	490-025B20-08L	20.0	25.0	83.0		1.2	0.18	40400	2	490R-08T308
	08	25	5.5	1	3	490-025B25-08M	25.0	25.0	88.0	32.0	1.2	0.28	40400	3	490R-08T308
32.0	08	25	5.5	1	3	490-032B25-08L	25.0	32.0	98.0		1.2	0.35	33900	3	490R-08T308
	08	32	5.5	1	3	490-032B32-08L	32.0	32.0	100.0	40.0	1.2	0.55	33900	3	490R-08T308
	08	25	5.5	1	4	490-032B25-08M	25.0	32.0	98.0		1.2	0.36	33900	4	490R-08T308
	08	32	5.5	1	4	490-032B32-08M	32.0	32.0	100.0	40.0	1.2	0.55	33900	4	490R-08T308
40.0	08	32	5.5	1	4	490-040B32-08M	32.0	40.0	112.0		1.2	0.70	29300	4	490R-08T308
	08	32	5.5	1	6	490-040B32-08H	32.0	40.0	112.0		1.2	0.72	29300	6	490R-08T308
	14	32	10.0	1	3	490-040B32-14M	32.0	40.0	112.0		3.0	0.65	26400	3	490R-1404
	14	32	10.0	1	4	490-040B32-14H	32.0	40.0	112.0		3.0	0.64	26400	4	490R-1404

J97
 O5
 Q5
 Q1
 Q35
 Q16